

SOH-57C-16 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 57, 16mm bore. Requires SOH-57-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-57C-16>

Technical Specifications

Brand	Sung-II Machinery	Maximum RPM	6000
Item	Drive coupling hub	Attachment Style	Clamp
Coupling Type	Oldham	Coupling Size	57
Material	Aluminum alloy	Bore Diameter	16mm
Rated Torque	34 N-m	Outside Diameter	57mm
Maximum Torque	68 N-m	Clamp Screw Fastening Torque	13 N-m
Maximum Angular Misalignment	1.5 degrees	Clamp Screw Size	M6
Maximum Parallel Misalignment	3.5mm	Requires	SOH-57-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-57C-16.pdf>
See store item page for other formats.