

SRB-16C-4-5 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 16, 4 x 5mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-16C-4-5>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	0.4 N-m
Maximum Torque	0.8 N-m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.15mm

Maximum RPM	27000
Attachment Style	Clamp
Coupling Size	16
Bore Diameter	4mm
Bore Diameter 2	5mm
Outside Diameter	16mm
Clamp Screw Fastening Torque	1 N-m
Clamp Screw Size	M2.6

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SRB-16C-4-5.pdf>
See store item page for other formats.