

US30M3000IU-B4 Cut Sheet



di-soric ultrasonic proximity sensor, tubular, 30mm diameter x 60mm body, nickel plated brass housing, diffuse, 0–10 VDC or 4–20 mA analog output, 300–3000mm sensing distance, IP67, 4-pin M12 quick-disconnect, IO-Link v1.1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/US30M3000IU-B4>

Technical Specifications

Brand	di-soric
Item	Proximity sensor
Sensor Type	Ultrasonic
Application	Standard duty, analog output and IO-Link
Shape	Tubular
Housing Size	30mm diameter x 60mm body
Housing Material	Nickel-plated brass
Barrel Type	Threaded
Sensing Method	Diffuse
Adjustable	No
Number of Wires	4
Analog Output	0–10 VDC or 4–20 mA
Sensing Distance	300–3000mm
Switching Frequency	3 Hz

Operating Voltage	18–30 VDC
Operating Temperature	-25 to +70 °C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	4-pin M12 quick-disconnect
IO-Link Compatible	Yes
Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E303138
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/US30M3000IU-B4.pdf>
See store item page for other formats.