

USQ12M400IU-T4 Cut Sheet



di-soric ultrasonic proximity sensor, rectangular, 12 x 12 x 75mm body, aluminum housing, top sensing, diffuse, 0–10 VDC or 4–20 mA analog output, 40–400mm sensing distance, IP67, 4-pin M8 quick-disconnect, IO-Link v1.1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/USQ12M400IU-T4>

Technical Specifications

Brand	di-soric
Item	Proximity sensor
Sensor Type	Ultrasonic
Application	Standard duty, analog output and IO-Link
Shape	Rectangular
Housing Size	12 x 12 x 75mm body
Housing Material	Aluminum
Sensing Face	Top sensing
Sensing Method	Diffuse
Adjustable	No
Number of Wires	4
Analog Output	0–10 VDC or 4–20 mA
Sensing Distance	40–400mm
Switching Frequency	10 Hz

Operating Voltage	18–30 VDC
Operating Temperature	-25 to +70 °C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	4-pin M8 quick-disconnect
IO-Link Compatible	Yes
Communication Port and Connection Type(s)	(1) 4-pin M8 (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes

Agency Approvals

UL Listed File #	E303138
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/USQ12M400IU-T4.pdf>
See store item page for other formats.