


# V30160-1 Cut Sheet



Southwire flexible control cable, unshielded, 5 conductors (includes ground), 20 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/V30160-1>

## Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cable	Jacket Material	TPE
Wire/Cable Type	Control	Jacket Color	Gray
UL Wire/Cable Type	PLTC-ER, ITC-ER and MTW	Nominal Overall Cable Diameter	0.307in
Application	General purpose	Bulk Length	Cut to length
Flexibility	Flexible	Package Type	1 to 50ft = Coil, 51 to 99ft = Coil, 100 to 402ft = 14 x 7in Reel, 403 to 582ft = 14 x 10in Reel, 583 to 905ft = 16 x 10in Reel, 906 to 1264ft = 18 x 10in Reel, 1265 to 1655ft = 18 x 13in Reel, 1656 to 3545ft = 24 x 17in Wooden Reel, 3546 to 5824ft = 30 x 17in Wooden Reel
Voltage Rating	300V (Types PLTC-ER, ITC-ER), 600V (Type MTW)		
Conductors	5 conductors (includes ground)		
Conductor Size	20 AWG		
Conductor Stranding	10-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	PVC/Nylon		
Conductor Insulation Color	Black with white numbers and green/yellow ground		

## Agency Approvals

UL Listed File #	E57497
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>