


STP-DRVA-BR-100 Cut Sheet



SureStep braking resistor, 100W, 10 ohm, encapsulated. For use with multiple stepper drives. Requires STP-DRVA-RC-050 regen clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STP-DRVA-BR-100>

Technical Specifications

Brand	SureStep
Item	Braking resistor
Brake Resistor Power Rating	100W
Resistance	10 ohm
Enclosure Type	Encapsulated
Built-in Temperature Switch	No
For Use With	Multiple stepper drives
Requires	STP-DRVA-RC-050 regen clamp

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/STP-DRVA-BR-100.pdf>
See store item page for other formats.