

# V3K1-S0-4Q Cut Sheet



Micro Detectors inductive proximity sensor, tubular, 18mm diameter x 64.5mm body, nickel-plated brass housing, N.C. (VAC) or N.O./N.C. (VDC) output, 10mm sensing distance, non-flush, 25 Hz (AC)/550 Hz (DC) switching frequency, IP67, 1/2in - 20UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/V3K1-S0-4Q>

## Technical Specifications

<b>Brand</b>	Micro Detectors
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Inductive
<b>Application</b>	Standard duty and AC powered
<b>Shape</b>	Tubular
<b>Housing Size</b>	18mm diameter x 64.5mm body
<b>Housing Material</b>	Nickel-plated brass
<b>Barrel Type</b>	Threaded
<b>Sensing Method</b>	Extended sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	2
<b>Operation Mode</b>	N.C. (VAC) or N.O./N.C. (VDC) output

<b>Sensing Distance</b>	10mm
<b>Mounting Type</b>	Non-flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	25 Hz (AC)/550 Hz (DC)
<b>Operating Voltage</b>	20-250 VAC/VDC
<b>Operating Temperature</b>	-25 to 70c
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP67
<b>Connection</b>	1/2in - 20UNF thread
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E187310
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>