

T23147 Cut Sheet



TITAN analog torque wrench, 3/8in drive, 60-960 lb-in set point, $\pm 4\%$ (DIN ISO 6789) accuracy, numerical torque value, click load signal, 15 degrees return angle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T23147>

Technical Specifications

Brand	TITAN
Item	Torque wrench
Display Type	Analog
Setpoint Range	60-960 lb-in
Accuracy	$\pm 4\%$ (DIN ISO 6789)
Scale	Numerical torque value
Indicator	Click load signal
Drive Size	3/8in
Lock Mechanism	Ballpoint socket

Directional Change	Switch lever
Return Angle	15 degrees
Handle Type	Knurled metal handle
Tool Features	Locking handle
Insulated	No
Ratcheting	Yes
Overall Length	14.2in (360mm)
Application	Ratcheting and torque driving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document