

# TE40-050-17-04 Cut Sheet



Stratus CFC-free air-to-air heat exchanger, 71.6 W/deg C (40 W/deg F), 120 VAC operating voltage, 50/60 Hz, 0.47A running current, side mount, cold-rolled steel, ANSI 61 gray, powder coat finish. For use with NEMA/UL Type 4 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TE40-050-17-04>

## Technical Specifications

<b>Brand</b>	Stratus
<b>Item</b>	CFC-free air-to-air Heat exchanger
<b>Cooling Capacity</b>	71.6 W/deg C (40 W/deg F)
<b>Operating Voltage</b>	120 VAC
<b>Frequency</b>	50/60 Hz
<b>Running Current</b>	0.47A
<b>Mounting</b>	Side
<b>Housing Material</b>	Cold-rolled steel

<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>For Use With</b>	NEMA/UL Type 4 enclosures
<b>Includes</b>	Mounting template and hardware
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Packaging Instruction: Y341</li><li>• UN Number: UN1230</li><li>• Hazard Type: Flammable Liquid</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	SA34086
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/TE40-050-17-04.pdf>  
See store item page for other formats.