

VFAS3-4004PC Cut Sheet



Toshiba AS3 series AC high-performance drive, UL Type 1, 460 VAC, 1/2 hp with 3-phase input, V/Hz, FOC, encoder or torque mode, A1 frame, Ethernet and RS-485, integrated dynamic braking. Optional EtherCAT, encoder and I/O cards available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFAS3-4004PC>

Technical Specifications

Brand	Toshiba
Item	Drive
Controller Type	High-performance
Series	AS3
Voltage Type	AC
Nominal Drive Input Voltage	460 VAC
Nominal Drive Output Voltage	460 VAC
Number of Input Phases	3
Number of Output Phases	3
Horsepower By Input Phase	1/2 hp with 3-phase input
Amperage Rating	1.5A
Variable Torque Amperage Rating	2.2A
Control Mode	V/Hz, FOC, encoder or torque
Integrated EMI Filter	Yes
Safe Torque Off (STO)	Built-in
Temperature Rating	-15 to +60 °C
Enclosure Type	UL Type 1
IP Rating	IP20
Mounting	Panel or wall
Frame Size	A1
Dynamic Braking	Integrated dynamic braking
Communication Port and Connection Type(s)	<ul style="list-style-type: none"> • (2) Ethernet (RJ45) • (1) RS-485 (RJ45)
Port Protocol(s)	<ul style="list-style-type: none"> • EtherNet/IP • webservice (non-secure HTTP) • Modbus RTU Slave • Modbus TCP
Port Speed(s)	<ul style="list-style-type: none"> • 10/100 Mbps • up to 38.4k baud
Input Signal	4–20 mA, voltage, potentiometer or pulse train input
Output Type	PWM output
Reverse Capability	Built-in
Internally Bypassed	No

Carrier Frequency Range	1–16 kHz
Output Frequency Range	0.1–590 Hz
Number of Analog Input Channels	3
Analog Input Signal Type	Current/voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	3
Input Resolution	11-bit
Input Current Signal Range	0–20 mA and 4–20 mA
Input Voltage Signal Range	±10 VDC
Number of Analog Output Channels	2
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	2
Output Resolution	10-bit
Output Current Signal Range	0–20 mA and 4–20 mA
Output Voltage Signal Range	0–10 VDC
Number of Discrete Input Points	8
Nominal Discrete Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	4
Number of Discrete Output Points	3
Nominal Discrete Output Voltage	250 VAC and 30 VDC
Discrete Output Type	Relay

VFAS3-4004PC Cut Sheet

Relay Configuration	(1) Form C (SPDT) relay, (2) Form A (SPST) relays
Number of Isolated Discrete Output Commons	3
Number of Points per Discrete Output Common	1
Load Current	2A/point relay
Fuse Type	User-supplied external fuse
Programming Language	User sequence
Connector Type	Screw terminals
For Use With	3-phase induction and permanent magnet AC motors
Includes	DC reactor (built-in), EMC filter (built-in) and conduit box
Additional Information	Optional EtherCAT, encoder and I/O cards available.
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.06• Replacement Battery: D0-MC-BAT• Generic Battery: CR2032

Agency Approvals

UL Listed File #	E204788
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	231252
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VFAS3-4004PC.pdf>
See store item page for other formats.