


THMWJ-20-1U-P-1 Cut Sheet

TE Wire & Cable Type J thermocouple extension wire, unshielded, 2 conductors, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-1U-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC

Conductor Insulation Color	White and red
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.15in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 1 to 250ft = Coil• 251 to 1645ft = 14 x 7in Reel• 1646 to 2350ft = 14 x 10in Reel• 2351 to 3637ft = 16 x 10in Reel• 3638 to 5122ft = 18 x 10in Reel• 5123 to 6658ft = 18 x 13in Reel• 6659 to 14302ft = 24 x 17in Wooden Reel• 14303 to 23514ft = 30 x 17in Wooden Reel• 23515 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement