


THMWJ-20-8S-P-1 Cut Sheet



TE Wire & Cable Type J thermocouple PLTC and ITC extension cable, shielded, 8 twisted pairs, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-8S-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Cable
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
UL Wire/Cable Type	PLTC and ITC
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	8 twisted pairs
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC
Conductor Insulation Color	White and red

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.492in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 25 to 50ft = Coil• 51 to 160ft = 14 x 7in Reel• 161 to 230ft = 14 x 10in Reel• 231 to 355ft = 16 x 10in Reel• 356 to 495ft = 18 x 10in Reel• 496 to 640ft = 18 x 13in Reel• 641 to 1435ft = 24 x 17in Wooden Reel• 1436 to 2295ft = 30 x 17in Wooden Reel• 2296 to 5000ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E54438
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement