

VFD-SC-14-4B-1P-1 Cut Sheet



Southwire flexible VFD/Servo cable, shielded, 4 conductors (includes ground), 14 AWG, 41-stranded, tinned copper, (1) shielded 16 AWG twisted pair, XLPE conductor insulation material, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFD-SC-14-4B-1P-1>

Technical Specifications

Brand	Southwire
Item	Cable
Wire/Cable Type	VFD/Servo
UL Wire/Cable Type	TC-ER and WTTC
Applicable Standards	UL 2277
Application	Drive and motor
Flexibility	Flexible
Voltage Rating	600V (Type TC), 1000V (Type WTTC, Flexible Motor Supply Cable)
Conductors	4 conductors (includes ground)
Conductor Size	14 AWG
Conductor Stranding	41-stranded
Conductor Material	Tinned copper
Auxiliary Conductors	(1) shielded 16 AWG twisted pair
Conductor Insulation Material	Cross linked polyethylene (XLPE)

Conductor Insulation Color	Black with white numbers and green/yellow ground with black and white twisted pair
Shielding	Overall foil and braid shielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.689in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 80ft = 14 x 7in Reel, 81 to 110ft = 14 x 10in Reel, 111 to 180ft = 16 x 10in Reel, 181 to 250ft = 18 x 10in Reel, 251 to 330ft = 18 x 13in Reel, 331 to 710ft = 24 x 17in Wooden Reel, 711 to 1180ft = 30 x 17in Wooden Reel, 1181 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E75755
CE	None
CSA File #	LL90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement