

THMWJ-UL-16-1S-P-1 Cut Sheet



TE Wire & Cable Type J thermocouple PLTC extension wire, shielded, 2 conductors, 16 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-UL-16-1S-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
UL Wire/Cable Type	PLTC
Applicable Standards	UL 13
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V rated (UL)
Conductors	2 conductors
Conductor Size	16 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC

Conductor Insulation Color	White and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.256in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 595ft = 14 x 7in Reel, 596 to 850ft = 14 x 10in Reel, 851 to 1305ft = 16 x 10in Reel, 1306 to 1820ft = 18 x 10in Reel, 1821 to 2370ft = 18 x 13in Reel, 2371 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E54438
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement