


THMWK-20-1U-S-1 Cut Sheet



TE Wire & Cable Type K thermocouple extension wire, unshielded, 2 conductors, 20 AWG, nickel-chromium and nickel-aluminum, braided vitreous silica conductor insulation material, white and white/red, braided vitreous silica jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-1U-S-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type K thermocouple
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Nickel-chromium and nickel-aluminum
Conductor Insulation Material	Braided vitreous silica

Conductor Insulation Color	White and white/red
Shielding	Unshielded
Jacket Material	Braided vitreous silica
Jacket Color	White
Nominal Overall Cable Diameter	0.162in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 50 to 99ft = Coil• 100 to 1000ft = 14 x 7in Reel

Agency Approvals

UL Listed File #	none
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement