


THMWK-20-1U-S-1 Cut Sheet



TE Wire & Cable Type K thermocouple extension wire, unshielded, 2 conductors, 20 AWG, nickel-chromium and nickel-aluminum, braided vitreous silica conductor insulation material, white and white/red, braided vitreous silica jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-1U-S-1>

Technical Specifications

| | |
|---------------------------------------|--|
| Brand | TE Wire & Cable |
| Item | Wire |
| Sensor Type | Type K thermocouple |
| Wire/Cable Type | Extension |
| Application | Temperature |
| Flexibility | Semi-flexible |
| Conductors | 2 conductors |
| Conductor Size | 20 AWG |
| Conductor Stranding | Solid |
| Conductor Material | Nickel-chromium and nickel-aluminum |
| Conductor Insulation Material | Braided vitreous silica |
| Conductor Insulation Color | White and white/red |
| Shielding | Unshielded |
| Jacket Material | Braided vitreous silica |
| Jacket Color | White |
| Nominal Overall Cable Diameter | 0.162in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 1 to 99ft = Coil• 100 to 1485ft = 14 x 7in Reel• 1486 to 2125ft = 14 x 10in Reel• 2126 to 3255ft = 16 x 10in Reel• 3256 to 4550ft = 18 x 10in Reel• 4551 to 5000ft = 18 x 13in Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | none |
| UL Recognized File # | none |
| UL Hazardous File # | none |
| CSA File # | none |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |