


THMWK-20-2S-P-1 Cut Sheet

TE Wire & Cable Type K thermocouple PLTC and ITC extension cable, shielded, 2 twisted pairs, 20 AWG, nickel-chromium and nickel-aluminum, PVC conductor insulation material, yellow and red, PVC jacket, yellow, cut to length.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-2S-P-1>

Technical Specifications

Brand	TE Wire & Cable	Conductor Insulation Color	Yellow and red
Item	Cable	Shielding	Shielded
Sensor Type	Type K thermocouple	Jacket Material	PVC
Wire/Cable Type	Extension	Jacket Color	Yellow
UL Wire/Cable Type	PLTC and ITC	Nominal Overall Cable Diameter	0.331in
Application	Temperature	Bulk Length	Cut to length
Flexibility	Semi-flexible	Package Type	<ul style="list-style-type: none">• 25 to 75ft = Coil• 76 to 355ft = 14 x 7in Reel• 356 to 510ft = 14 x 10in Reel• 511 to 780ft = 16 x 10in Reel• 781 to 1090ft = 18 x 10in Reel• 1091 to 1415ft = 18 x 13in Reel• 1416 to 3170ft = 24 x 17in Wooden Reel• 3171 to 5000ft = 30 x 17in Wooden Reel
Voltage Rating	300V		
Conductors	2 twisted pairs		
Conductor Size	20 AWG		
Conductor Stranding	Solid		
Conductor Material	Nickel-chromium and nickel-aluminum		
Conductor Insulation Material	PVC		

Agency Approvals

UL Listed File #	E54438
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement