

# VFK1-A0-2M Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 18mm diameter x 70mm body, 316L stainless steel housing, N.O. output, 12mm sensing distance, non-flush, 25 Hz (AC)/300 Hz (DC) switching frequency, IP68 IP69K, 1/2in - 20UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFK1-A0-2M>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Inductive
<b>Application</b>	Food and beverage and AC powered
<b>Shape</b>	Tubular
<b>Housing Size</b>	18mm diameter x 70mm body
<b>Housing Material</b>	316L stainless steel
<b>Barrel Type</b>	Threaded
<b>Sensing Method</b>	Standard sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	2
<b>Operation Mode</b>	N.O. output
<b>Sensing Distance</b>	12mm

<b>Mounting Type</b>	Non-flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	25 Hz (AC)/300 Hz (DC)
<b>Operating Voltage</b>	20-140 VAC/VDC
<b>Operating Temperature</b>	0 to 100C
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP68 IP69K
<b>Connection</b>	1/2in - 20UNF thread
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately. For harsh duty / food and beverage applications

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>