


THMWK-20-8S-P-1 Cut Sheet



TE Wire & Cable Type K thermocouple PLTC and ITC extension cable, shielded, 8 twisted pairs, 20 AWG, nickel-chromium and nickel-aluminum, PVC conductor insulation material, yellow and red, PVC jacket, yellow, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-8S-P-1>

Technical Specifications

Brand	TE Wire & Cable	Shielding	Shielded
Item	Cable	Jacket Material	PVC
Sensor Type	Type K thermocouple	Jacket Color	Yellow
Wire/Cable Type	Extension	Nominal Overall Cable Diameter	0.492in
UL Wire/Cable Type	PLTC and ITC	Bulk Length	Cut to length
Application	Temperature	Package Type	<ul style="list-style-type: none">• 25 to 50ft = Coil• 51 to 160ft = 14 x 7in Reel• 161 to 230ft = 14 x 10in Reel• 231 to 355ft = 16 x 10in Reel• 356 to 495ft = 18 x 10in Reel• 496 to 640ft = 18 x 13in Reel• 641 to 1435ft = 24 x 17in Wooden Reel• 1436 to 2295ft = 30 x 17in Wooden Reel• 2296 to 5000ft = Large Wooden Reel
Flexibility	Semi-flexible		
Voltage Rating	300V		
Conductors	8 twisted pairs		
Conductor Size	20 AWG		
Conductor Stranding	Solid		
Conductor Material	Nickel-chromium and nickel-aluminum		
Conductor Insulation Material	PVC		
Conductor Insulation Color	Yellow and red		

Agency Approvals

UL Listed File #	E54438
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement