

# VFL75-150S-2D Cut Sheet



ProSense vibration fork liquid level switch, any orientation mount, 1.89in insertion length, 316L stainless steel wetted parts, -40 to 302 deg F, 3/4in male NPT process connection, AC/DC, 2-wire, N.O. or N.C., EN 175301-803-A connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFL75-150S-2D>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Level switch
<b>Sensor Type</b>	Vibration fork
<b>Media Type</b>	Water, oil and chemicals
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	1.89in
<b>Process Connection</b>	3/4in male NPT
<b>Process Temperature</b>	-40 to 302 deg F
<b>Output</b>	AC/DC, 2-wire, N.O. or N.C.
<b>Operating Voltage</b>	20-253 VAC/DC
<b>Wetted Parts</b>	316L stainless steel
<b>Sensing Element Material</b>	316L stainless steel
<b>Electrical Connection</b>	EN 175301-803-A connector
<b>IP Rating</b>	IP65
<b>NEMA Rating</b>	4X

## Agency Approvals

<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	600062
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/VFL75-150S-2D.pdf>  
See store item page for other formats.