

# VFS75-26-1001 Cut Sheet



ProSense liquid flow sensor, vortex, 3/4in female NPT process connection, 1.3 to 26.4 GPM, 80 to 1585 GPH, 14 to 194 deg F, Output: switch or frequency, Output 2: switch or frequency, 18 to 30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFS75-26-1001>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Flow sensor
<b>Media Type</b>	Liquid
<b>Sensing Type</b>	Vortex
<b>Process Connection</b>	3/4in female NPT
<b>Measuring Range</b>	1.3 to 26.4 GPM
<b>Measuring Range 2</b>	80 to 1585 GPH
<b>Measuring Range 3</b>	14 to 194 deg F
<b>Output</b>	Switch (N.O./N.C.) or frequency, PNP/NPN selectable
<b>Output 2</b>	Switch (N.O./N.C.) or frequency, PNP/NPN selectable
<b>Operating Voltage</b>	18 to 30 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>