

# THMWT-20-1U-P-1 Cut Sheet

TE Wire & Cable Type T thermocouple extension wire, unshielded, 2 conductors, 20 AWG, copper and copper-nickel, PVC conductor insulation material, blue and red, PVC jacket, blue, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWT-20-1U-P-1>

## Technical Specifications

<b>Brand</b>	TE Wire & Cable
<b>Item</b>	Wire
<b>Sensor Type</b>	Type T thermocouple
<b>Wire/Cable Type</b>	Extension
<b>Application</b>	Temperature
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	2 conductors
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	Solid
<b>Conductor Material</b>	Copper and copper-nickel
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Blue and red

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Blue
<b>Nominal Overall Cable Diameter</b>	0.15in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 250ft = Coil, 251 to 1645ft = 14 x 7in Reel, 1646 to 2350ft = 14 x 10in Reel, 2351 to 3637ft = 16 x 10in Reel, 3638 to 5122ft = 18 x 10in Reel, 5123 to 6658ft = 18 x 13in Reel, 6659 to 14302ft = 24 x 17in Wooden Reel, 14303 to 23514ft = 30 x 17in Wooden Reel, 23515 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>