


WG-325-020-DC Cut Sheet



IronHorse heavy duty worm gearbox, 20:1 ratio, NEMA 182TC input, dual, 1.375in diameter output shaft, nominal 4.74 hp at 1.0 SF, 2875 lb-in mechanical output torque, 3-1/4in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-325-020-DC>

Technical Specifications

Brand	IronHorse
Item	Gearbox
Application	General purpose
Duty Rating	Heavy duty
Gearbox Type	Worm
Gear Ratio	20:1
Speed Rating	1750 rpm input / 90 rpm output
Input Configuration	NEMA 182TC
Input Power Rating	Nominal 4.74 hp at 1.0 SF
Output Configuration	Dual

Gearbox Output Shaft Diameter	1.375in
Mechanical Output Torque	2875 lb-in
Thermal Output Torque	2011 lb-in
Center Distance	3-1/4in
Housing Material	Cast iron
Mounting	Tapped-base
Finish	Anti-corrosion primer and paint
Lubrication Type	Pre-filled with synthetic lube
Oil Seal Type	Double-lip

Agency Approvals

UL Listed File #	none
UL Recognized File #	none
UL Hazardous File #	none
CE	None
CSA File #	none
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WG-325-020-DC.pdf>
See store item page for other formats.