

WGA-30M-ACC4 Cut Sheet



IronHorse gearbox double output shaft, 0.625in. For use with WGA-30M NEMA series gearboxes. (4) keys, (2) spacers and (2) retaining rings included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WGA-30M-ACC4>

Technical Specifications

Brand	IronHorse
Item	Shaft
Shaft Type	Gearbox double output
Size	0.625in
For Use With	WGA-30M NEMA series gearboxes
Includes	(4) keys, (2) spacers and (2) retaining rings

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WGA-30M-ACC4.pdf>
See store item page for other formats.