

WPT25-20-0150H Cut Sheet



HydroMode pressure transmitter, 0 to 150 psig range, +/-1% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/4in male NPT process connection, 8 to 32 VDC operating voltage, 4-pin M12 quick-disconnect, NSF/ANSI/CAN 61 and NSF 372.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WPT25-20-0150H>

Technical Specifications

Brand	HydroMode
Item	Pressure transmitter
Pressure Range	0 to 150 psig
Accuracy	+/-1% of full range
Sensing Element Material	Stainless steel
Analog Output	4-20 mA
Process Connection	1/4in male NPT
Operating Voltage	8 to 32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Media Type	Liquid and gases
Potable Water Certifications	NSF/ANSI/CAN 61 and NSF 372
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	MH66873
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/WPT25-20-0150H.pdf>
See store item page for other formats.