

TP19U230B1 Cut Sheet



Fandis Virdis series exhaust fan, top mount, 338 CFM, 230 VAC operating voltage, NEMA 12, indoor use only, 6.89 x 6.89in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TP19U230B1>

Technical Specifications

Brand	Fandis
Series	Virdis series
Airflow Direction	Exhaust
Item	Fan
Mounting	Top
With Air Flaps	No
Free Airflow	338 CFM
Airflow with Grill and Filter(s)	297 CFM
Operating Voltage	230 VAC
Frequency	60 Hz
Power Consumption	81W
Current Draw	360 mA

Electrical Connection	Terminal block
Maximum Static Pressure	465Pa
Operating Temperature	14 to 131 deg F
Average Noise Level	71 dBA
NEMA Rating	12
Application	Indoor use only
IP Rating	IP24
Enclosure Cutout	6.89 x 6.89in
Color	RAL 7035 light gray
Includes	Mounting screws
Additional Information	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Refer to technical specifications for 50Hz performance data

Agency Approvals

UL Listed File #	E500932
UL Recognized File #	E237844
UL Hazardous File #	None
CE	View CE declarations
CSA File #	260922
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TP19U230B1.pdf>
See store item page for other formats.