

XBL-EIPT Cut Sheet



LS Electric XGB communication module, EtherNet/IP, 2 ports, (2) Ethernet 10/100Base-T (RJ45) port(s). For use with LS Electric XGB series PLCs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBL-EIPT>

Technical Specifications

Brand	LS Electric XGB
Item	Communication module
Number of Ports	2
Buffered Ports	No
Communication Port and Connection Type(s)	(2) Ethernet 10/100Base-T (RJ45)
Port Protocol(s)	EtherNet/IP Client/Server
Port Speed(s)	10/100 Mbps auto-detect
For Use With	LS Electric XGB series PLCs
Programming Software	XG5000 programming software v4.76_2024_02_22 or later and XEM PLC firmware 2.4 or later
Additional Information	Built-in switch for daisy chain connection as server, data logging function

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XBL-EIPT.pdf>
See store item page for other formats.