

TP19U230B1 Cut Sheet



Fandis Virdis series exhaust fan, top mount, 338 CFM, 230 VAC operating voltage, NEMA 12, indoor use only, 6.89 x 6.89in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TP19U230B1>

Technical Specifications

Brand	Fandis	Electrical Connection	Terminal block
Series	Virdis series	Maximum Static Pressure	465Pa
Airflow Direction	Exhaust	Operating Temperature	14 to 131 deg F
Item	Fan	Average Noise Level	71 dBA
Mounting	Top	NEMA Rating	12
With Air Flaps	No	Application	Indoor use only
Free Airflow	338 CFM	IP Rating	IP24
Airflow with Grill and Filter(s)	297 CFM	Enclosure Cutout	6.89 x 6.89in
Operating Voltage	230 VAC	Color	RAL 7035 light gray
Frequency	60 Hz	Includes	Mounting screws
Power Consumption	81W	Additional Information	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Refer to technical specifications for 50Hz performance data
Current Draw	360 mA		

Agency Approvals

UL Listed File #	E500932
UL Recognized File #	E237844
UL Hazardous File #	None
CE	View CE declarations
CSA File #	260922
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document