


XTH2-0-UNV-P Cut Sheet



ProSense programmable temperature transmitter, isolated, RTD, thermocouple, millivolt or potentiometer input, deg F or deg C, current output, 10-36 VDC operating voltage, DIN Form B connection head mount, push-in terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH2-0-UNV-P>

Technical Specifications

Brand	ProSense
Item	Programmable temperature transmitter
Isolation	Isolated
Field Configurable	Yes
Input Potentiometer Resistance	10-2000 Ohms
Input RTD Signal Types	Cu50, Cu100, Ni100, Ni120, Pt100, Pt200, Pt500 and Pt1000
Input Thermocouple Signal Type	J, K, L, N, R, S, T, U, A, B, C, D, E
Input Voltage Signal Range	-20 to 100 mV

Programmable Temperature Range	Deg F or deg C
Output Current Signal Range	4-20 mA and 20-4 mA
Operating Voltage	10-36 VDC
Housing Material	Polycarbonate
Mounting	DIN Form B connection head
Electrical Connection	Push-in terminals
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	601711
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XTH2-0-UNV-P.pdf>
See store item page for other formats.