

# Y502 Cut Sheet



Marathon MicroMAX premium efficiency AC induction motor, high-performance inverter duty, 1/3hp, 3-phase, 230 VAC, 1800rpm, TENV, 56C frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Y502>

## Technical Specifications

<b>Brand</b>	Marathon	<b>Shaft Diameter</b>	5/8in
<b>Item</b>	Motor	<b>Shaft Material</b>	1144 Stressproof (C-223) steel
<b>Series</b>	MicroMAX	<b>Motor Frame</b>	56C
<b>Efficiency Group</b>	Premium efficiency	<b>Frame Material</b>	Rolled steel
<b>Efficiency</b>	74	<b>Electrically Reversible</b>	Yes
<b>Voltage Type</b>	AC	<b>Insulation Class</b>	Class H
<b>Motor Type</b>	Induction	<b>IP Rating</b>	IP43
<b>Motor Application</b>	High-performance inverter duty	<b>Constant Torque Rating</b>	1000:1
<b>Horsepower Rating</b>	1/3hp	<b>Variable Torque Rating</b>	10:1
<b>Number of Phases</b>	3	<b>Service Factor</b>	1.0
<b>Voltage Rating</b>	230 VAC	<b>Integrated Brake</b>	No
<b>Synchronous Speed</b>	1800rpm	<b>NEMA Design</b>	Design B
<b>Nameplate RPM</b>	1725rpm	<b>Junction Box Orientation</b>	F3
<b>Overload Type</b>	None	<b>Mounting</b>	C-face/rigid base
<b>Enclosure Type</b>	TENV	<b>Mounting Orientation</b>	Horizontal
<b>Shaft Type</b>	Round with square key	<b>Manufacturer Part Number</b>	056H17T2013

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E49747
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR37479
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>