

# USQ12M400FPG3-T4 Cut Sheet



di-soric ultrasonic proximity sensor, rectangular, 12 x 12 x 82mm body, aluminum housing, top sensing, foreground suppression, push-pull NPN or PNP, N.O./N.C. selectable output, 40–400mm sensing distance, IP67, 4-pin M8 quick-disconnect, IO-Link v1.1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/USQ12M400FPG3-T4>

## Technical Specifications

<b>Brand</b>	di-soric
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Ultrasonic
<b>Application</b>	Standard duty and IO-Link
<b>Shape</b>	Rectangular
<b>Housing Size</b>	12 x 12 x 82mm body
<b>Housing Material</b>	Aluminum
<b>Sensing Face</b>	Top sensing
<b>Sensing Method</b>	Foreground suppression
<b>Adjustable</b>	No
<b>Number of Wires</b>	4
<b>Switching Output</b>	Push-pull NPN or PNP
<b>Operation Mode</b>	N.O./N.C. selectable output
<b>Sensing Distance</b>	40–400mm

<b>Switching Frequency</b>	10 Hz
<b>Operating Voltage</b>	18–30 VDC
<b>Operating Temperature</b>	-25 to +70 °C
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP67
<b>Connection</b>	4-pin M8 quick-disconnect
<b>IO-Link Compatible</b>	Yes
<b>Communication Port and Connection Type(s)</b>	(1) 4-pin M8 (IO-Link) port(s)
<b>Port Protocol(s)</b>	IO-Link Class A Device
<b>Port Speed(s)</b>	IO-Link COM2
<b>IO-Link Version</b>	IO-Link v1.1
<b>Standard I/O Mode Supported</b>	Yes

## Agency Approvals

<b>UL Listed File #</b>	E303138
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/USQ12M400FPG3-T4.pdf>  
See store item page for other formats.