


V30158-1 Cut Sheet



Southwire flexible control cable, unshielded, 4 conductors (includes ground), 20 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/V30158-1>

Technical Specifications

| | | | |
|--------------------------------------|--|---------------------------------------|--|
| Brand | Southwire | Shielding | Unshielded |
| Item | Cable | Jacket Material | TPE |
| Wire/Cable Type | Control | Jacket Color | Gray |
| UL Wire/Cable Type | PLTC-ER, ITC-ER and MTW | Nominal Overall Cable Diameter | 0.285in |
| Application | General purpose | Bulk Length | Cut to length |
| Flexibility | Flexible | Package Type | 1 to 50ft = Coil, 51 to 99ft = Coil, 100 to 480ft = 14 x 7in Reel, 481 to 680ft = 14 x 10in Reel, 681 to 1060ft = 16 x 10in Reel, 1061 to 1500ft = 18 x 10in Reel, 1501 to 1950ft = 18 x 13in Reel, 1951 to 4190ft = 24 x 17in Wooden Reel, 4191 to 6890ft = 30 x 17in Wooden Reel |
| Voltage Rating | 300V (Types PLTC-ER, ITC-ER), 600V (Type MTW) | | |
| Conductors | 4 conductors (includes ground) | | |
| Conductor Size | 20 AWG | | |
| Conductor Stranding | 10-stranded | | |
| Conductor Material | Bare copper | | |
| Conductor Insulation Material | PVC/Nylon | | |
| Conductor Insulation Color | Black with white numbers and green/yellow ground | | |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E57497 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 90458 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |