


V30186-1 Cut Sheet



Southwire flexible control cable, unshielded, 12 conductors (includes ground), 20 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/V30186-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cable	Jacket Material	TPE
Wire/Cable Type	Control	Jacket Color	Gray
UL Wire/Cable Type	PLTC-ER, ITC-ER and MTW	Nominal Overall Cable Diameter	0.453in
Applicable Standards	ECOLAB	Bulk Length	Cut to length
Application	General purpose	Package Type	• 20 to 50ft = Coil
Flexibility	Flexible		• 51 to 190ft = 14 x 7in Reel
Voltage Rating	300V (Types PLTC-ER, ITC-ER), 600V (Type MTW)		• 191 to 270ft = 14 x 10in Reel
Conductors	12 conductors (includes ground)		• 271 to 415ft = 16 x 10in Reel
Conductor Size	20 AWG		• 416 to 580ft = 18 x 10in Reel
Conductor Stranding	10-stranded		• 581 to 755ft = 18 x 13in Reel
Conductor Material	Bare copper		• 756 to 1690ft = 24 x 17in Wooden Reel
Conductor Insulation Material	PVC/Nylon		• 1691 to 2705ft = 30 x 17in Wooden Reel
Conductor Insulation Color	Black with white numbers and green/yellow ground		• 2706 to 5000ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E57497
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement