

Datawind Filterfans®



The Datawind series Filterfans feature a compact design with integrated thermostat control and indicator light. Available in three sizes covering airflow needs from 38 to 560 CFM. Each kit includes the Filterfans unit, dual thermostat (FLZ 543), power cable, and mounting hardware for a complete installation.



18182000039

Features

- Three sizes: DPF 22000 (38 CFM), DPF 33000 SL (152 CFM), DPF 67000 (560 CFM)
- Integrated red indicator light for temperature alarm
- Includes FLZ 543 dual thermostat with separate fan and alarm setpoints
- IP55 / NEMA Type 12 rated
- Operating temperature: -40 to +131 °F [-40 to +55 °C]
- Complete kit: fan, filter mat, thermostat, power cable, gaskets, mounting hardware

Listings

- UL: E175229
- CSA: 2293770



Datawind Filterfans								
Part Number	Price	Model	Color	Voltage	Airflow	Power	Current	Drawing Link
<u>18182000039</u>	\$618.00	DPF 22000	RAL 9003 white	115 VAC	38 CFM	19W	0.24A	<u>PDF</u>
<u>18182000040</u>	\$618.00	DPF 22000	RAL 9004 black	115 VAC	38 CFM	19W	0.24A	<u>PDF</u>
<u>18182000041</u>	\$653.00	DPF 22000	RAL 9003 white	230 VAC	38 CFM	19W	0.18A	<u>PDF</u>
<u>18182000042</u>	\$653.00	DPF 22000	RAL 9004 black	230 VAC	38 CFM	19W	0.18A	<u>PDF</u>
<u>18182000043</u>	\$818.00	DPF 33000 SL	RAL 9003 white	115 VAC	152 CFM	40W	0.56A	<u>PDF</u>
<u>18182000044</u>	\$818.00	DPF 33000 SL	RAL 9004 black	115 VAC	152 CFM	40W	0.56A	<u>PDF</u>
<u>18182000045</u>	\$859.00	DPF 33000 SL	RAL 9003 white	230 VAC	152 CFM	45W	0.31A	<u>PDF</u>
<u>18182000046</u>	\$859.00	DPF 33000 SL	RAL 9004 black	230 VAC	152 CFM	45W	0.31A	<u>PDF</u>
<u>18182000047</u>	\$1,242.00	DPF 67000	RAL 9003 white	115 VAC	560 CFM	196W	1.71A	<u>PDF</u>
<u>18182000048</u>	\$1,242.00	DPF 67000	RAL 9004 black	115 VAC	560 CFM	196W	1.71A	<u>PDF</u>
<u>18182000049</u>	\$1,299.00	DPF 67000	RAL 9003 white	230 VAC	560 CFM	197W	0.86A	<u>PDF</u>
<u>18182000050</u>	\$1,299.00	DPF 67000	RAL 9004 black	230 VAC	560 CFM	197W	0.86A	<u>PDF</u>

Datawind Filterfans Specifications	
Running Temperature	-40 to +131 °F [-40 to +55 °C]
Storage Temperature	-40 to +158 °F [-40 to +70 °C]
Frequency	50/60 Hz
Filtration Efficiency	91%
Filter Mat Class (EN 779)	G4
Fuse	6A
Protection Rating	IP55 / NEMA Type 12
Included Thermostat	FLZ 543 (N.O./N.O.)