





Supplementary Protector / Disconnect Terminal Block Sockets



DN-DIS series Disconnect Terminal Blocks offer the flexibility of opening a circuit without removing any wiring. Available with or without LED indication in 12VDC and 24VDC, they can also be used as a socket for the DN-SUPP series Supplementary Protectors by simply removing the Disconnect Blade.



**DN-DISx Series:
EURO F2.5 / EURO F4**



**DN-DISxL Series: EURO F2
with LED / EURO F4 with LED**

Ordering Information

| | Part Number | Trip Indicator | Pcs/ Pkg | Price | Part Number | Trip Indicator | Pcs/ Pkg | Price |
|------------------------------------|---------------------|----------------|-------------|---------|---------------------|----------------|-------------|---------|
| Gray Socket with Disconnect | <i>DN-DIS2</i> | — | 50 | \$76.00 | <i>DN-DIS4</i> | — | 50 | \$76.00 |
| | <i>DN-DIS2MN</i> | — | 10 | \$18.50 | <i>DN-DIS4MN</i> | — | 10 | \$18.50 |
| | <i>DN-DIS2L12</i> | 12 VAC/DC LED | 50 | \$98.00 | <i>DN-DIS4L12</i> | 12 VAC/DC LED | 50 | \$98.00 |
| | <i>DN-DIS2L12MN</i> | 12 VAC/DC LED | 10 | \$22.50 | <i>DN-DIS4L12MN</i> | 12 VAC/DC LED | 10 | \$22.50 |
| | <i>DN-DIS2L24</i> | 24 VAC/DC LED | 50 | \$98.00 | <i>DN-DIS4L24</i> | 24 VAC/DC LED | 50 | \$98.00 |
| | <i>DN-DIS2L24MN</i> | 24 VAC/DC LED | 10 | \$22.50 | <i>DN-DIS4L24MN</i> | 24 VAC/DC LED | 10 | \$22.50 |

Technical Specifications

| | | | | | | |
|------------------------------|--|--------------------------------------|---------------|-------------------|--------------------------------------|---------------|
| Stripping Length | 5mm [0.20 in] | | | 6mm [0.24 in] | | |
| Tightening Torque | 0.5 N·m [4.4 lb·in] | | | 0.8 N·m [7 lb·in] | | |
| UL Approval* | 300V | 10A with SUPP 20A with disconnect | 24-12 AWG* | 300V | 10A with SUPP 25A with disconnect | 24-10 AWG* |
| Operating Temperature | Ambient air temperature: -20°C to 85°C [-4°F to 185°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F] | | | | | |
| SCCR Rating | 100kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components | | | | | |
| CE Conformity | CE (EN 60947-1 / 60947-7-3) | | | | | |
| Agency File # | UL E179129 | | | | | |

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Accessories

| | | | | | | | |
|--------------------------------|------------------------------|--------------------|---------|-----------------------------|--------------------|---------|---------|
| End Cover/ Spacer** | <i>DN-FESPA</i> | 50 | \$15.50 | <i>DN-FESPA</i> | 50 | \$15.50 | |
| | <i>DN-FESPA-10</i> | 10 | \$3.00 | <i>DN-FESPA-10</i> | 10 | \$3.00 | |
| Separator | <i>DN-FESEP</i> | 50 | \$15.50 | <i>DN-FESEP</i> | 50 | \$15.50 | |
| | <i>DN-FESEP-10</i> | 10 | \$3.00 | <i>DN-FESEP-10</i> | 10 | \$3.00 | |
| 35mm DIN Rail | 7.5 mm high | <i>DN-R35S1</i> | 10 | \$28.00 | <i>DN-R35S1</i> | 10 | \$28.00 |
| | | <i>DN-R35S1-2</i> | 2 | \$9.25 | <i>DN-R35S1-2</i> | 2 | \$9.25 |
| | 15mm high | <i>DN-R35HS1</i> | 10 | \$50.00 | <i>DN-R35HS1</i> | 10 | \$50.00 |
| | | <i>DN-R35HS1-2</i> | 2 | \$12.50 | <i>DN-R35HS1-2</i> | 2 | \$12.50 |
| End Brackets | <i>DN-EB35</i> | 50 | \$40.00 | <i>DN-EB35</i> | 50 | \$40.00 | |
| | <i>DN-EB35MN</i> | 20 | \$18.50 | <i>DN-EB35MN</i> | 20 | \$18.50 | |
| | <i>DN-EB35-A</i> | 50 | \$28.50 | <i>DN-EB35-A</i> | 50 | \$28.50 | |
| | <i>DN-EB35-A-10</i> | 10 | \$7.75 | <i>DN-EB35-A-10</i> | 10 | \$7.75 | |
| | <i>DN-QEB35</i> | 50 | \$25.50 | <i>DN-QEB35</i> | 50 | \$25.50 | |
| | <i>DN-QEB35-10</i> | 10 | \$7.75 | <i>DN-QEB35-10</i> | 10 | \$7.75 | |
| Angled Support Bracket | <i>DN-ASB1</i> | 50 | \$50.00 | <i>DN-ASB1</i> | 50 | \$50.00 | |
| Disconnect Blade | <i>DN-DIS-BLADE</i> | 50 | \$22.00 | <i>DN-DIS-BLADE</i> | 50 | \$22.00 | |
| | <i>DN-DIS-BMN</i> | 10 | \$5.75 | <i>DN-DIS-BMN</i> | 10 | \$5.75 | |
| Marking Tags | <i>DN-LA or DN-LT series</i> | 500/ 100 | various | <i>DN-L or DN-LT series</i> | 500/ 100 | various | |


*For copper wire only

**Use one End Cover / Spacer per DN-FEx Terminal Block Socket when using DN-SUPP-x supplementary protector

Note: For more information on accessories, see the DINnectors Accessories section of this chapter.



Terminal Block Sockets



F2.5/
F4 SP socket
block

F2.5/
F4 SP socket
block w/LED

DN-FE series terminal block sockets accept separately available circuit disconnects or supplementary protectors. The DN-FE blocks are available either with or without a trip-indicating LED and they are 35mm DIN-rail mountable. The LED blocks are polarity-sensitive, with the LED side negative.



DN-FEx Series:
EURO F2.5 / EURO F4



DN-FExL Series: EURO F2 with LED / EURO F4 with LED

| Ordering Information | | | | | | | | |
|----------------------|-------------|----------------|---------|---------|-------------|----------------|---------|---------|
| | Part Number | Trip Indicator | Pcs/Pkg | Price | Part Number | Trip Indicator | Pcs/Pkg | Price |
| Socket Only | DN-FE2 | – | 50 | \$66.00 | DN-FE4 | – | 50 | \$66.00 |
| | DN-FE2-5 | – | 5 | \$7.25 | DN-FE4-5 | – | 5 | \$7.25 |
| | DN-FE2L12 | 12 VAC/DC LED | 50 | \$90.00 | DN-FE4L12 | 12 VAC/DC LED | 50 | \$90.00 |
| | DN-FE2L12-5 | 12 VAC/DC LED | 5 | \$9.25 | DN-FE4L12-5 | 12 VAC/DC LED | 5 | \$9.25 |
| | DN-FE2L24 | 24 VAC/DC LED | 50 | \$90.00 | DN-FE4L24 | 24 VAC/DC LED | 50 | \$90.00 |
| | DN-FE2L24-5 | 24 VAC/DC LED | 5 | \$9.25 | DN-FE4L24-5 | 24 VAC/DC LED | 5 | \$9.25 |


| Technical Specifications | | | | | | | | |
|--------------------------|--|-----------------------------------|------------|--|-------------------|-----------------------------------|------------|--|
| Stripping Length | 5mm [0.24 in] | | | | 6mm [0.24 in] | | | |
| Tightening Torque | 0.5 N·m [4.4 lb·in] | | | | 0.8 N·m [7 lb·in] | | | |
| UL Approval* | 300V | 10A with SUPP/20A with disconnect | 24-12 AWG* | | 300V | 10A with SUPP/25A with disconnect | 24-10 AWG* | |
| Operating Temperature | Ambient air temperature: -20°C to 105°C [-4°F to 221°F] / Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F] | | | | | | | |
| SCCR Rating | 100kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components | | | | | | | |
| CE Conformity | CE (EN 60947-1 / EN 60947-7-3) | | | | | | | |
| Agency File # | UL E179129 | | | | | | | |

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.


| Accessories | | | | | | | | |
|-------------------------|--------------|-----------------------|---------------|--------------|----------------------|---------------|---------|--|
| End Cover/Spacer** | DN-FESPA | 50 | \$15.50 | DN-FESPA | 50 | \$15.50 | | |
| | DN-FESPA-10 | 10 | \$3.00 | DN-FESPA-10 | 10 | \$3.00 | | |
| Separator | DN-FESEP | 50 | \$15.50 | DN-FESEP | 50 | \$15.50 | | |
| | DN-FESEP-10 | 10 | \$3.00 | DN-FESEP-10 | 10 | \$3.00 | | |
| Jumper**** | 12-pole | DN-12JFE | 10 | \$35.50 | DN-12JFE | 10 | \$35.50 | |
| Jumper Cutting Tool | | DN-JFECUT | 1 | \$55.00 | DN-JFECUT | 1 | \$55.00 | |
| 35mm DIN Rail | 7.5 mm high | DN-R35S1 | 10 | \$28.00 | DN-R35S1 | 10 | \$28.00 | |
| | | DN-R35S1-2 | 2 | \$9.25 | DN-R35S1-2 | 2 | \$9.25 | |
| | 15mm high | DN-R35HS1 | 10 | \$50.00 | DN-R35HS1 | 10 | \$50.00 | |
| | | DN-R35HS1-2 | 2 | \$12.50 | DN-R35HS1-2 | 2 | \$12.50 | |
| End Brackets | DN-EB35 | 50 | \$40.00 | DN-EB35 | 50 | \$40.00 | | |
| | DN-EB35MN | 20 | \$18.50 | DN-EB35MN | 20 | \$18.50 | | |
| | DN-EB35-A | 50 | \$28.50 | DN-EB35-A | 50 | \$28.50 | | |
| | DN-EB35-A-10 | 10 | \$7.75 | DN-EB35-A-10 | 10 | \$7.75 | | |
| | DN-QEB35 | 50 | \$25.50 | DN-QEB35 | 50 | \$25.50 | | |
| DN-QEB35-10 | 10 | \$7.75 | DN-QEB35-10 | 10 | \$7.75 | | | |
| Angled Support Bracket | | DN-ASB1 | 50 | \$50.00 | DN-ASB1 | 50 | \$50.00 | |
| Disconnect Blade | | DN-DIS-BLADE | 50 | \$22.00 | DN-DIS-BLADE | 50 | \$22.00 | |
| | | DN-DIS-BMN | 10 | \$5.75 | DN-DIS-BMN | 10 | \$5.75 | |
| Supplementary Protector | | DN-SUPP-x*** | see next page | | DN-SUPP-x*** | see next page | | |
| Marking Tags | | DN-LA or DN-LT series | 500/100 | various | DN-L or DN-LT series | 500/100 | various | |

*For copper wire only
 **When aligned along, use one End Covers/Spacers per DN-FEx. When aligned in a row, use two End Covers/Spacers per DN-FEx
 ***Trip ratings available from 0.25 A to 10A
 ****For jumper installation, use two End Covers/Spacers per DN-FEx
 Note: For more information on accessories, see the DINnectors Accessories section of this chapter.


DN-FEx with DN-SUPP-x Supplementary Protector



DN-DIS-xxx dimensions are the same as DN-FExxx dimensions.



When aligned alone, use
DN-FESEP



When aligned in a row, use
2pcs **DN-FESPA** for **DN-FE2**
2pcs **DN-FESEP** for **DN-FE4**




Supplementary Protectors for Terminal Block Sockets


| Supplementary Protectors | | | | | | | |
|--------------------------|-----------|---------------|---------------------|---|---|----------|------------|
| Part Number | Reference | Rated Current | Internal Resistance | Type | Fits Socket | Pcs /Pkg | Price /Pkg |
| DN-SUPP-P25 | 435T0025 | 0.25 A | 14Ω | UL1077 Single Pole Push On Push Off Push to Reset | Terminal Block Socket Types: DN-FEx or DN-DISx if disconnect blade is removed | 20 | \$200.00 |
| DN-SUPP-P25-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-P5 | 435T0050 | 0.5 A | 3.4 Ω | | | 20 | \$200.00 |
| DN-SUPP-P5-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-1 | 435T0100 | 1A | 0.9 Ω | | | 20 | \$200.00 |
| DN-SUPP-1-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-2 | 435T0200 | 2A | 0.25 Ω | | | 20 | \$200.00 |
| DN-SUPP-2-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-3 | 435T0300 | 3A | 0.11 Ω | | | 20 | \$200.00 |
| DN-SUPP-3-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-4 | 435T0400 | 4A | 0.07 Ω | | | 20 | \$200.00 |
| DN-SUPP-4-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-6 | 435T0600 | 6A | | | | 20 | \$200.00 |
| DN-SUPP-6-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-8 | 435T0800 | 8A | ≤0.05 Ω | | | 20 | \$200.00 |
| DN-SUPP-8-1 | | | | | | 1 | \$10.50 |
| DN-SUPP-10 | 435T1000 | 10A | | 20 | \$200.00 | | |
| DN-SUPP-10-1 | | | | 1 | \$10.50 | | |



DN-SUPP-x
Supplementary Protector
(plugs into DN-FE EURO F series socket)




| Supplementary Protector Specifications DN-SUPP-x Series | |
|--|---|
| Voltage Rating (UL – U.S. & Canada) | 250VAC / 72VDC |
| Voltage Rating (VDE) | 250VAC / 65VDC |
| Typical Life Span | 6,000 operations @ 1 x IN (low inductance) 3,000 operations @ 1 x IN (inductive) 500 operations @ 2 x IN (inductive) |
| Insulation Coordination (IEC 60664 & 60664A) | Rated impulse withstand voltage 2.5 kV; reinforced insulation in operating area; pollution degree 2 |
| Dielectric Strength (IEC 60664 & 60664A) | Operating area: 3,000VAC Installation area: 1,500VAC |
| Insulation Resistance | >100MΩ @ 500VDC |
| Interrupting Capacity (UL 1077), SCCR | 2,000A @ 250VAC; 200A @ 65VDC, SCCR = 2kA with series overcurrent protection |
| Interrupting Capacity ICN | 0.1 to 5A: 6 x IN 6 to 10A: 8 x IN |
| Degree of Protection (IEC 60529 / DIN 40050) | Operating area IP40; terminal area IP00 |
| Vibration (without terminal block) | 5g (57-500 Hz) ±0.38 mm (10-57 Hz) to IEC 60068-2-6, test Fc, 10 frequency cycles/axis and to EN 50155 |
| Shock (without terminal block) | 25g (11ms) to IEC 60068-2-27, test Ea |
| Corrosion | 96 hours @ 5% salt mist to IEC 60068-2-11, test Ka |
| Usage Temperature | -4°F to 140°F (-20°C to 60°C) |
| Humidity | 240 hours @ 95% RH to IEC 60068-2-3, test Ca |
| Mass (weight) | 15g (0.53 oz) |
| Agency Approval | UL file # E320462 (435T Series); VDE |
| Mounting Restrictions | When 2 or more devices are mounted side by side, each device should only carry 80% of its rating, or must be derated accordingly. |



DINnectors[®] Accessories

**DN-LB (blank)
shown on right**




DN-L

- **Fits terminal block types:** All except Screwless DINnectors, DN-T12-A, DN-M10-A, DN-MG, and DN-TL series
- **Material:** Thermoplastic with heat embossed black print

Note:

1. The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500 tags.
2. The DN-L tags fit all DINnectors 6mm wide and wider.
3. The DN-L tags fit all DINnectors 6mm wide and wider but will leave gap between tags on blocks wider than 6mm.

Dimensions



| Marking Sequence | Part# | Pcs/Pkg | Price |
|--|----------------|---------|---------|
| 1-50 | DN-L50 | 500 | \$33.00 |
| 51-100 | DN-L100 | 500 | \$33.00 |
| 101-150 | DN-L150 | 500 | \$33.00 |
| 151-200 | DN-L200 | 500 | \$33.00 |
| 201-250 | DN-L250 | 500 | \$33.00 |
| 251-300 | DN-L300 | 500 | \$33.00 |
| 301-350 | DN-L350 | 500 | \$33.00 |
| 351-400 | DN-L400 | 500 | \$33.00 |
| 401-450 | DN-L450 | 500 | \$33.00 |
| Blank | DN-LB | 500 | \$22.50 |
| L1, L2, L3, L, N, GND, +, -, COM, COM* | DN-LS | 500 | \$33.00 |



DN-QL

- **Fits terminal block types:** Screwless DN-Q series
- **Material:** Thermoplastic with heat embossed black print. Packaged 100 labels per card, and five cards per box.

Note:

1. The marking sequence (i.e. 1-100) is printed five times in each package of 500 tags.

Dimensions



DN-QLS Shown

| Marking Sequence | Part # | Pcs/Pkg | Price |
|--------------------------------------|-----------------|---------|---------|
| 1-100 | DN-QL100 | 500 | \$25.50 |
| 101-200 | DN-QL200 | 500 | \$25.50 |
| 201-300 | DN-QL300 | 500 | \$25.50 |
| 301-400 | DN-QL400 | 500 | \$25.50 |
| 401-500 | DN-QL500 | 500 | \$25.50 |
| Blank Tags | DN-QLB | 500 | \$22.00 |
| L1, L2, L3, L, N, ⊕, +, -, COM, COM* | DN-QLS | 500 | \$29.00 |



**DN-LAB (blank) shown on left;
part of DN-LA100 on right**


DN-LA

- **Fits terminal block types:** DN-T12-A series
- **Material:** Thermoplastic with heat embossed black print

Note:

1. The marking sequence (i.e. 1-100) is printed five times in each package of 500 tags.
2. The DN-T12-A series is 5mm wide, so the 6mm wide DN-L tags do not fit these blocks.
3. The DN-LA tags fit all DINnectors 5mm wide and wider but will leave a gap between tags on blocks wider than 5mm.

Dimensions



| Marking Sequence | Part# | Pcs/Pkg | Price |
|--|-----------------|---------|---------|
| 1-100 | DN-LA100 | 500 | \$33.00 |
| 101-200 | DN-LA200 | 500 | \$33.00 |
| 201-300 | DN-LA300 | 500 | \$33.00 |
| 301-400 | DN-LA400 | 500 | \$33.00 |
| Blank Tags | DN-LAB | 500 | \$33.00 |
| L1, L2, L3, L, N, GND, +, -, COM, COM* | DN-LAS | 500 | \$33.00 |


DN-LAT-A

- **Fits terminal block types:** Triple level DN-TL14
- **Material:** Thermoplastic with heat embossed black print

Note:

1. The marking sequence (i.e. 1-100) is printed five times in each package of 500 tags.

Dimensions



| Marking Sequence | Part # | Pcs/Pkg | Price |
|--------------------------------------|--------------------|---------|---------|
| 1-100 | DN-LAT100-A | 500 | \$29.00 |
| 101-200 | DN-LAT200-A | 500 | \$29.00 |
| 201-300 | DN-LAT300-A | 500 | \$29.00 |
| 301-400 | DN-LAT400-A | 500 | \$29.00 |
| 401-500 | DN-LAT500-A | 500 | \$29.00 |
| 501-600 | DN-LAT600-A | 500 | \$29.00 |
| Blank Tags | DN-LATB-A | 500 | \$21.50 |
| L1, L2, L3, L, N, ⊕, +, -, COM, COM* | DN-LATS-A | 500 | \$29.00 |



**DN-LTA marker shown top; DN-LT60 marker shown middle;
DN-LTGND shown bottom**


DN-LT

- **Fits terminal block types:** All except Screwless DINnectors (see DN-QL series)
- **Material:** Thermoplastic with heat embossed black print

Note:

1. These marking tags allow the flexibility of creating custom marking sequences on site.
2. The DN-M10-A support a maximum of three digits (tags), while other DINnectors support up to four digits (tags)

Dimensions



| Marking Sequence | Part# | Pcs/Pkg | Price |
|------------------|------------------|---------|--------|
| 1-5 | DN-LT15 | 100 | \$6.00 |
| 6-0 | DN-LT60 | 100 | \$6.00 |
| 1 | DN-LT1 | 100 | \$6.00 |
| 2 | DN-LT2 | 100 | \$6.00 |
| 3 | DN-LT3 | 100 | \$6.00 |
| 4 | DN-LT4 | 100 | \$6.00 |
| 5 | DN-LT5 | 100 | \$6.00 |
| 6 | DN-LT6 | 100 | \$6.00 |
| 7 | DN-LT7 | 100 | \$6.00 |
| 8 | DN-LT8 | 100 | \$6.00 |
| 9 | DN-LT9 | 100 | \$6.00 |
| 0 | DN-LT0 | 100 | \$6.00 |
| Unprinted | DN-LTBLNK | 100 | \$6.00 |
| A | DN-LTA | 100 | \$6.00 |
| B | DN-LTB | 100 | \$6.00 |
| C | DN-LTC | 100 | \$6.00 |
| D | DN-LTD | 100 | \$6.00 |
| E | DN-LTE | 100 | \$6.00 |
| F | DN-LTF | 100 | \$6.00 |
| G | DN-LTG | 100 | \$6.00 |
| H | DN-LTH | 100 | \$6.00 |
| I | DN-LTI | 100 | \$6.00 |
| J | DN-LTJ | 100 | \$6.00 |
| K | DN-LTK | 100 | \$6.00 |
| L | DN-LTL | 100 | \$6.00 |
| M | DN-LTM | 100 | \$6.00 |
| N | DN-LTN | 100 | \$6.00 |
| - | - | - | - |
| P | DN-LTP | 100 | \$6.00 |
| Q | DN-LTQ | 100 | \$6.00 |
| R | DN-LTR | 100 | \$6.00 |
| S | DN-LTS | 100 | \$6.00 |
| T | DN-LTT | 100 | \$6.00 |
| U | DN-LTU | 100 | \$6.00 |
| V | DN-LTV | 100 | \$6.00 |
| W | DN-LTW | 100 | \$6.00 |
| X | DN-LTX | 100 | \$6.00 |
| Y | DN-LTY | 100 | \$6.00 |
| Z | DN-LTZ | 100 | \$6.00 |
| ⊕ | DN-LTGND | 100 | \$6.00 |
| + | DN-LTPOS | 100 | \$6.00 |
| - | DN-LTNEG | 100 | \$6.00 |
| ~ | DN-LTAC | 100 | \$6.00 |
| = | DN-LTDC | 100 | \$6.00 |

DINnectors® Accessories


Terminal Marking Accessories



DN-EMLBL1




DN-EMLBL2




DN-EMLBL3

| Part # | Description | For Use With | Pcs/Pkg | Price Each |
|------------------|------------------------|---|---------|------------|
| DN-EMLBL1 | Blank labels | DN-EMPEG1 pin protectors for DN-xEMxx plug-in terminal blocks | 100 | \$5.50 |
| DN-EMLBL2 | Labels printed 1 – 12 | | 100 | \$7.50 |
| DN-EMLBL3 | Labels printed 13 – 24 | | 100 | \$7.50 |



DN-MTA marking tag adapter

DN-MTA dimensions



| Part# | Description | Pcs/Pkg | Price Each |
|---------------|--|---------|------------|
| DN-MTA | Marking tag adapter holds up to six DN-LT tags | 50 | \$8.25 |

Note: DN-MTA adapter does not fit DN-T12-A terminal blocks.

Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink

| Part# | Description | Pcs/Pkg | Price Each |
|--------------|---------------------------------|---------|------------|
| DN-MP | Indelible black ink marking pen | 1 | \$3.75 |



Marking pen

Wire Marking Accessories



DN-WMTAG1 wire tags & DN-WM-x wire tag holders

| Part # | Description | For Use With | Pcs/Pkg | Price Each |
|------------------|--|------------------------------|---------|------------|
| DN-WMTAG1 | Wire tag – blank | all DN-WM-x wire tag holders | 525 | \$35.00 |
| DN-WM-1 | Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire | DN-WMTAG1 | 200 | \$7.25 |
| DN-WM-2 | Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16–11 AWG wire | | 200 | \$7.25 |
| DN-WM-3 | Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire | | 100 | \$4.75 |
| DN-WM-4 | Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire | | 100 | \$4.25 |