







# Supplementary Protector / Disconnect Terminal Block Sockets

DN-DIS series Disconnect Terminal Blocks offer the flexibility of opening a circuit without removing any wiring. Available with or without LED indication in 12VDC and 24VDC, they can also be used as a socket for the DN-SUPP series Supplementary Protectors by simply removing the Disconnect Blade.



**DN-DISx Series:  
EURO F2.5 / EURO F4**

**DN-DISxL Series: EURO F2  
with LED / EURO F4 with LED**



**WARNING: DO NOT DISCONNECT UNDER LOAD**

## Ordering Information

	Part Number	Trip Indicator	Qty	Price	Part Number	Trip Indicator	Qty	Price
Gray Socket with Disconnect	<a href="#">DN-DIS2</a>	-	50	\$128.00	<a href="#">DN-DIS4</a>	-	50	\$128.00
	<a href="#">DN-DIS2MN</a>	-	10	\$31.50	<a href="#">DN-DIS4MN</a>	-	10	\$31.50
	<a href="#">DN-DIS2L12</a>	12 VAC/DC LED	50	\$163.00	<a href="#">DN-DIS4L12</a>	12 VAC/DC LED	50	\$163.00
	<a href="#">DN-DIS2L12MN</a>	12 VAC/DC LED	10	\$37.00	<a href="#">DN-DIS4L12MN</a>	12 VAC/DC LED	10	\$37.00
	<a href="#">DN-DIS2L24</a>	24 VAC/DC LED	50	\$163.00	<a href="#">DN-DIS4L24</a>	24 VAC/DC LED	50	\$163.00
	<a href="#">DN-DIS2L24MN</a>	24 VAC/DC LED	10	\$37.00	<a href="#">DN-DIS4L24MN</a>	24 VAC/DC LED	10	\$37.00

## Technical Specifications

<b>Stripping Length</b>	5mm [0.20 in]			6mm [0.24 in]		
<b>Tightening Torque</b>	0.5 N·m [4.4 lb·in]			0.8 N·m [7 lb·in]		
<b>UL Approval*</b>	300V	10A with SUPP 20A with disconnect	24-12 AWG*	300V	10A with SUPP 25A with disconnect	24-10 AWG*
<b>Operating Temperature</b>	Ambient air temperature: -20 to 85°C [-4 to 185°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]					
<b>SCCR Rating</b>	10kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components					
<b>CE Conformity</b>	CE (EN 60947-1 / 60947-7-3)					
<b>Agency File #</b>	UL E179129					


## Accessories

		Part Number	Qty	Price	Part Number	Qty	Price	
<b>End Cover/Spacer**</b>		<a href="#">DN-FESPA</a>	50	\$26.50	<a href="#">DN-FESPA</a>	50	\$26.50	
		<a href="#">DN-FESPA-10</a>	10	\$5.25	<a href="#">DN-FESPA-10</a>	10	\$5.25	
<b>Separator</b>		<a href="#">DN-FESEP</a>	50	\$26.50	<a href="#">DN-FESEP</a>	50	\$26.50	
		<a href="#">DN-FESEP-10</a>	10	\$5.25	<a href="#">DN-FESEP-10</a>	10	\$5.25	
<b>35mm DIN Rail</b>	7.5 mm high	<a href="#">DN-R35S1</a>	10	\$39.00	<a href="#">DN-R35S1</a>	10	\$39.00	
		<a href="#">DN-R35S1-2</a>	2	\$11.00	<a href="#">DN-R35S1-2</a>	2	\$11.00	
	15mm high	<a href="#">DN-R35HS1</a>	10	\$68.00	<a href="#">DN-R35HS1</a>	10	\$68.00	
		<a href="#">DN-R35HS1-2</a>	2	\$16.50	<a href="#">DN-R35HS1-2</a>	2	\$16.50	
<b>End Brackets</b>		<a href="#">DN-EB35</a>	50	\$67.00	<a href="#">DN-EB35</a>	50	\$67.00	
		<a href="#">DN-EB35MN</a>	20	\$31.50	<a href="#">DN-EB35MN</a>	20	\$31.50	
		<a href="#">DN-EB35-A</a>	50	\$47.50	<a href="#">DN-EB35-A</a>	50	\$47.50	
		<a href="#">DN-EB35-A-10</a>	10	\$12.00	<a href="#">DN-EB35-A-10</a>	10	\$12.00	
		<a href="#">DN-QEB35</a>	50	\$42.50	<a href="#">DN-QEB35</a>	50	\$42.50	
		<a href="#">DN-QEB35-10</a>	10	\$11.50	<a href="#">DN-QEB35-10</a>	10	\$11.50	
<b>Angled Support Bracket</b>		<a href="#">DN-ASB1</a>	50	\$107.00	<a href="#">DN-ASB1</a>	50	\$107.00	
<b>Disconnect Blade</b>		<a href="#">DN-DIS-BLADE</a>	50	\$36.00	<a href="#">DN-DIS-BLADE</a>	50	\$36.00	
		<a href="#">DN-DIS-BMN</a>	10	\$9.75	<a href="#">DN-DIS-BMN</a>	10	\$9.75	
<b>Marking Tags</b>	DN-LA or DN-LT series		500/ 100	various	DN-L or DN-LT series		500/ 100	various


\*For copper wire only  
 \*\*Use one End Cover / Spacer per DN-FEx Terminal Block Socket when using DN-SUPP-x supplementary protector  
 Note: For more information on accessories, see the DINnectors Accessories section of this chapter.

# DINnectors® Terminal Block Sockets


DN-FE series terminal block sockets accept separately available circuit disconnects or supplementary protectors. The DN-FE blocks are available either with or without a trip-indicating LED and they are 35mm DIN rail mountable. The LED blocks are polarity-sensitive, with the LED side negative.



**DN-FEx Series:**  
EURO F2.5 / EURO F4



**DN-FExL Series: EURO F2 with LED / EURO F4 with LED**



## Ordering Information

	Part Number	Trip Indicator	Qty	Price	Part Number	Trip Indicator	Qty	Price
Socket Only	<a href="#">DN-FE2</a>	-	50	\$112.00	<a href="#">DN-FE4</a>	-	50	\$112.00
	<a href="#">DN-FE2-5</a>	-	5	\$12.50	<a href="#">DN-FE4-5</a>	-	5	\$12.50
	<a href="#">DN-FE2L12</a>	12 VAC/DC LED	50	\$150.00	<a href="#">DN-FE4L12</a>	12 VAC/DC LED	50	\$150.00
	<a href="#">DN-FE2L12-5</a>	12 VAC/DC LED	5	\$15.00	<a href="#">DN-FE4L12-5</a>	12 VAC/DC LED	5	\$15.00
	<a href="#">DN-FE2L24</a>	24 VAC/DC LED	50	\$150.00	<a href="#">DN-FE4L24</a>	24 VAC/DC LED	50	\$150.00
	<a href="#">DN-FE2L24-5</a>	24 VAC/DC LED	5	\$15.00	<a href="#">DN-FE4L24-5</a>	24 VAC/DC LED	5	\$15.00

## Technical Specifications

<b>Stripping Length</b>	5mm [0.20 in]			6mm [0.24 in]		
<b>Tightening Torque</b>	0.5 N·m [4.4 lb·in]			0.8 N·m [7 lb·in]		
<b>UL Approval*</b>	300V	10A with SUPP/20A with disconnect	24-12 AWG*	300V	10A with SUPP/25A with disconnect	24-10 AWG*
<b>Operating Temperature</b>	Ambient air temperature: -20 to 105°C [-4 to 221°F] / Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]					
<b>SCCR Rating</b>	100kA					
<b>CE Conformity</b>	CE (EN 60947-1 / EN 60947-7-3)					
<b>Agency File #</b>	UL E179129					

## Accessories

<b>End Cover/Spacer**</b>	<a href="#">DN-FESPA</a>	50	\$26.50	<a href="#">DN-FESPA</a>	50	\$26.50	
	<a href="#">DN-FESPA-10</a>	10	\$5.25	<a href="#">DN-FESPA-10</a>	10	\$5.25	
<b>Separator</b>	<a href="#">DN-FESEP</a>	50	\$26.50	<a href="#">DN-FESEP</a>	50	\$26.50	
	<a href="#">DN-FESEP-10</a>	10	\$5.25	<a href="#">DN-FESEP-10</a>	10	\$5.25	
<b>Jumper****</b>	12-pole	<a href="#">DN-12JFE</a>	10	\$60.00	<a href="#">DN-12JFE</a>	10	\$60.00
<b>Jumper Cutting Tool</b>		<a href="#">DN-JFECUT</a>	1	\$92.00	<a href="#">DN-JFECUT</a>	1	\$92.00
<b>35mm DIN Rail</b>	7.5 mm high	<a href="#">DN-R35S1</a>	10	\$39.00	<a href="#">DN-R35S1</a>	10	\$39.00
		<a href="#">DN-R35S1-2</a>	2	\$11.00	<a href="#">DN-R35S1-2</a>	2	\$11.00
	15mm high	<a href="#">DN-R35HS1</a>	10	\$68.00	<a href="#">DN-R35HS1</a>	10	\$68.00
		<a href="#">DN-R35HS1-2</a>	2	\$16.50	<a href="#">DN-R35HS1-2</a>	2	\$16.50
<b>End Brackets</b>	<a href="#">DN-EB35</a>	50	\$67.00	<a href="#">DN-EB35</a>	50	\$67.00	
	<a href="#">DN-EB35MN</a>	20	\$31.50	<a href="#">DN-EB35MN</a>	20	\$31.50	
	<a href="#">DN-EB35-A</a>	50	\$47.50	<a href="#">DN-EB35-A</a>	50	\$47.50	
	<a href="#">DN-EB35-A-10</a>	10	\$12.00	<a href="#">DN-EB35-A-10</a>	10	\$12.00	
	<a href="#">DN-QEB35</a>	50	\$42.50	<a href="#">DN-QEB35</a>	50	\$42.50	
	<a href="#">DN-QEB35-10</a>	10	\$11.50	<a href="#">DN-QEB35-10</a>	10	\$11.50	
<b>Angled Support Bracket</b>	<a href="#">DN-ASB1</a>	50	\$107.00	<a href="#">DN-ASB1</a>	50	\$107.00	
<b>Disconnect Blade</b>	<a href="#">DN-DIS-BLADE</a>	50	\$36.00	<a href="#">DN-DIS-BLADE</a>	50	\$36.00	
	<a href="#">DN-DIS-BMN</a>	10	\$9.75	<a href="#">DN-DIS-BMN</a>	10	\$9.75	
<b>Supplementary Protector</b>	<a href="#">DN-SUPP-x***</a>	see next page		<a href="#">DN-SUPP-x***</a>	see next page		
<b>Marking Tags</b>	DN-LA or DN-LT series	500/100	various	DN-L or DN-LT series	500/100	various	

\*For copper wire only


\*\*When aligned along, use one End Covers/Spacers per DN-FEx. When aligned in a row, use two End Covers/Spacers per DN-FEx

\*\*\*Trip ratings available from 0.25 A to 10A


\*\*\*\*For jumper installation, use two End Covers/Spacers per DN-FEx

Note: For more information on accessories, see the DINnectors Accessories section of this chapter.


DN-FEx with DN-SUPP-x Supplementary Protector



When aligned alone, use **DN-FESEP**



When aligned in a row, use  
2pcs **DN-FESPA** for **DN-FE2**  
2pcs **DN-FESEP** for **DN-FE4**



DN-FE2, DN-FE2Lxx  
DN-FE4, DN-FE4Lxx  
DN-FE2xxx DN-FE4xxx  
DN-DIS-xxx dimensions are the same as DN-FExxx dimensions.




# Supplementary Protectors for Terminal Block Sockets


Supplementary Protectors							
Part Number	Reference	Rated Current	Internal Resistance	Type	Fits Socket	Qty	Price
<a href="#">DN-SUPP-P25</a>	435T0025	0.25 A	14Ω	UL1077 Single Pole Push On Push Off Push to Reset	Terminal Block Socket Types: DN-FEx or DN-DISx if disconnect blade is removed	20	\$332.00
<a href="#">DN-SUPP-P25-1</a>						1	\$17.50
<a href="#">DN-SUPP-P5</a>	435T0050	0.5 A	3.4 Ω			20	\$332.00
<a href="#">DN-SUPP-P5-1</a>						1	\$17.50
<a href="#">DN-SUPP-1</a>	435T0100	1A	0.9 Ω			20	\$332.00
<a href="#">DN-SUPP-1-1</a>						1	\$17.50
<a href="#">DN-SUPP-2</a>	435T0200	2A	0.25 Ω			20	\$332.00
<a href="#">DN-SUPP-2-1</a>						1	\$17.50
<a href="#">DN-SUPP-3</a>	435T0300	3A	0.11 Ω			20	\$332.00
<a href="#">DN-SUPP-3-1</a>						1	\$17.50
<a href="#">DN-SUPP-4</a>	435T0400	4A	0.07 Ω			20	\$332.00
<a href="#">DN-SUPP-4-1</a>						1	\$17.50
<a href="#">DN-SUPP-6</a>	435T0600	6A				20	\$332.00
<a href="#">DN-SUPP-6-1</a>						1	\$17.50
<a href="#">DN-SUPP-8</a>	435T0800	8A	≤0.05 Ω			20	\$332.00
<a href="#">DN-SUPP-8-1</a>						1	\$17.50
<a href="#">DN-SUPP-10</a>	435T1000	10A		20	\$332.00		
<a href="#">DN-SUPP-10-1</a>				1	\$17.50		



**DN-SUPP-x**  
Supplementary Protector  
(plugs into DN-FE EURO F series socket)



Supplementary Protector Specifications DN-SUPP-x Series	
<b>Voltage Rating (UL – U.S. &amp; Canada)</b>	250VAC / 72VDC
<b>Voltage Rating (VDE)</b>	250VAC / 65VDC
<b>Typical Life Span</b>	6,000 operations @ 1 x IN (low inductance) 3,000 operations @ 1 x IN (inductive) 500 operations @ 2 x IN (inductive)
<b>Insulation Coordination (IEC 60664 &amp; 60664A)</b>	Rated impulse withstand voltage 2.5 kV; reinforced insulation in operating area; pollution degree 2
<b>Dielectric Strength (IEC 60664 &amp; 60664A)</b>	Operating area: 3,000VAC Installation area: 1,500VAC
<b>Insulation Resistance</b>	>100MΩ @ 500VDC
<b>Interrupting Capacity (UL 1077), SCCR</b>	2,000A @ 250VAC; 200A @ 65VDC, SCCR = 2kA with series overcurrent protection
<b>Interrupting Capacity ICN</b>	0.1 to 5A: 6 x IN 6 to 10A: 8 x IN
<b>Degree of Protection (IEC 60529 / DIN 40050)</b>	Operating area IP40; terminal area IP00
<b>Vibration (without terminal block)</b>	5g (57-500 Hz) ±0.38 mm (10-57 Hz) to IEC 60068-2-6, test Fc, 10 frequency cycles/axis and to EN 50155
<b>Shock (without terminal block)</b>	25g (11ms) to IEC 60068-2-27, test Ea
<b>Corrosion</b>	96 hours @ 5% salt mist to IEC 60068-2-11, test Ka
<b>Usage Temperature</b>	-4 to 140°F (-20 to 60°C)
<b>Humidity</b>	240 hours @ 95% RH to IEC 60068-2-3, test Ca
<b>Mass (weight)</b>	15g (0.53 oz)
<b>Agency Approval</b>	UL file # E320462 (435T Series); VDE
<b>Mounting Restrictions</b>	When 2 or more devices are mounted side by side, each device should only carry 80% of its rating, or must be derated accordingly.



The time/current characteristic curve depends upon the prevailing ambient temperature. In order to eliminate nuisance tripping, multiply the supplementary protector current ratings by the derating factor shown below:

Ambient Temperature	°F	-22	-4	14	32	73.4	104	122	140
	°C	-30	-20	-10	0	23	40	50	60
Temp Derating Factor		0.8	0.76	0.84	0.92	1	1.08	1.16	1.24

**Note:** When 2 or more devices are mounted side by side, each device should only carry 80% of its rating, or must be derated accordingly.


**DINnectors® Accessories**

## Marking Tags Cross Reference Charts - Screw-type


<b>DINector Marking Tags Cross Reference - Screw-type</b>					
<i>Block Type</i>	<i>DN-L</i>	<i>DN-LA</i>	<i>DN-LT</i>	<i>DN-LAT</i>	<i>DN-EMLBL</i>
<i>DN-T12</i>	-	X	X	-	-
<i>DN-T10</i>	X	-	X	-	-
<i>DN-T8</i>	X	-	X	-	-
<i>DN-T6</i>	X	-	X	-	-
<i>DN-T4</i>	X	-	X	-	-
<i>DN-T1/0</i>	X	-	X	-	-
<i>DN-T3/0</i>	X	-	X	-	-
<i>DN-D10</i>	X	-	X	-	-
<i>DN-D10X</i>	X	-	X	-	-
<i>DN-D10LED</i>	X	-	X	-	-
<i>DN-D10DR</i>	X	-	X	-	-
<i>DN-TL14</i>	-	-	-	X	-
<i>DN-THERM</i>	X	-	X	-	-
<i>DN-EMXM1</i>	-	X	X	-	X
<i>DN-EMXDV</i>	-	X	X	-	X
<i>DN-M10</i>	-	-	X	-	-
<i>DN-MG10</i>	-	-	X	-	-
<i>DN-G10</i>	X	-	X	-	-
<i>DN-G8</i>	X	-	X	-	-
<i>DN-G6</i>	X	-	X	-	-
<i>DN-G4</i>	X	-	X	-	-
<i>DN-G1/0</i>	X	-	X	-	-
<i>DN-F6</i>	X	-	X	-	-
<i>DN-F10</i>	X	-	X	-	-
<i>DN-DIS2</i>	-	X	X	-	-
<i>DN-DIS4</i>	X	-	X	-	-
<i>DN-FE2</i>	-	X	X	-	-
<i>DN-FE4</i>	X	-	X	-	-
<i>DN-DIS10</i>	X	-	X	-	-
<i>DN-KBD12</i>	-	X	X	-	-

Continued on next page

# DINnectors® Accessories


## Marking Tags

Marking Tags DN-L Series			
Part Number	Marking Sequence	Qty	Price
<a href="#">DN-L50</a>	1-50	500	\$56.00
<a href="#">DN-L100</a>	51-100	500	\$56.00
<a href="#">DN-L150</a>	101-150	500	\$56.00
<a href="#">DN-L200</a>	151-200	500	\$56.00
<a href="#">DN-L250</a>	201-250	500	\$56.00
<a href="#">DN-L300</a>	251-300	500	\$56.00
<a href="#">DN-L350</a>	301-350	500	\$56.00
<a href="#">DN-L400</a>	351-400	500	\$56.00
<a href="#">DN-L450</a>	401-450	500	\$56.00
<a href="#">DN-LB</a>	Blank	500	\$38.00
<a href="#">DN-LS</a>	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	\$56.00




- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500.
- The DN-L tags fit all DINnectors 6mm wide and wider.
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LA Series			
Part Number	Marking Sequence	Qty	Price
<a href="#">DN-LA100</a>	1-100	500	\$56.00
<a href="#">DN-LA200</a>	101-200	500	\$56.00
<a href="#">DN-LA300</a>	201-300	500	\$56.00
<a href="#">DN-LA400</a>	301-400	500	\$56.00
<a href="#">DN-LAB</a>	Blank Tags	500	\$56.00
<a href="#">DN-LAS</a>	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	\$56.00




- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DINnectors 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LAT Series			
Part Number	Marking Sequence	Qty	Price
<a href="#">DN-LAT100-A</a>	1-100	500	\$49.00
<a href="#">DN-LAT200-A</a>	101-200	500	\$49.00
<a href="#">DN-LAT300-A</a>	201-300	500	\$49.00
<a href="#">DN-LAT400-A</a>	301-400	500	\$49.00
<a href="#">DN-LAT500-A</a>	401-500	500	\$49.00
<a href="#">DN-LAT600-A</a>	501-600	500	\$49.00
<a href="#">DN-LATB-A</a>	Blank Tags	500	\$35.50
<a href="#">DN-LATS-A</a>	L1, L2, L3, L, N, +, -, COM,COM*	500	\$49.00



- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-QL Series			
Part Number	Marking Sequence	Qty	Price
<a href="#">DN-QL100</a>	1-100	500	\$42.50
<a href="#">DN-QL200</a>	101-200	500	\$42.50
<a href="#">DN-QL300</a>	201-300	500	\$42.50
<a href="#">DN-QL400</a>	301-400	500	\$42.50
<a href="#">DN-QL500</a>	401-500	500	\$42.50
<a href="#">DN-QLB</a>	Blank Tags	500	\$36.00
<a href="#">DN-QLS</a>	L1, L2, L3, L, N, +, -, COM,COM*	500	\$49.00




- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

# DINnectors® Accessories


## Marking Tags continued

Marking Tags DN-LT Series			
Part Number	Marking Sequence	Qty	Price
<a href="#">DN-LT15</a>	1-5	100	\$10.00
<a href="#">DN-LT60</a>	6-0	100	\$10.00
<a href="#">DN-LT1</a>	1	100	\$10.00
<a href="#">DN-LT2</a>	2	100	\$10.00
<a href="#">DN-LT3</a>	3	100	\$10.00
<a href="#">DN-LT4</a>	4	100	\$10.00
<a href="#">DN-LT5</a>	5	100	\$10.00
<a href="#">DN-LT6</a>	6	100	\$10.00
<a href="#">DN-LT7</a>	7	100	\$10.00
<a href="#">DN-LT8</a>	8	100	\$10.00
<a href="#">DN-LT9</a>	9	100	\$10.00
<a href="#">DN-LT0</a>	0	100	\$10.00
<a href="#">DN-LTBLNK</a>	Unprinted	100	\$10.00
<a href="#">DN-LTA</a>	A	100	\$10.00
<a href="#">DN-LTB</a>	B	100	\$10.00
<a href="#">DN-LTC</a>	C	100	\$10.00
<a href="#">DN-LTD</a>	D	100	\$10.00
<a href="#">DN-LTE</a>	E	100	\$10.00
<a href="#">DN-LTF</a>	F	100	\$10.00
<a href="#">DN-LTG</a>	G	100	\$10.00
<a href="#">DN-LTH</a>	H	100	\$10.00
<a href="#">DN-LTI</a>	I	100	\$10.00
<a href="#">DN-LTJ</a>	J	100	\$10.00
<a href="#">DN-LTK</a>	K	100	\$10.00
<a href="#">DN-LTL</a>	L	100	\$10.00
<a href="#">DN-LTM</a>	M	100	\$10.00
<a href="#">DN-LTN</a>	N	100	\$10.00
-	-	-	-
<a href="#">DN-LTP</a>	P	100	\$10.00
<a href="#">DN-LTQ</a>	Q	100	\$10.00
<a href="#">DN-LTR</a>	R	100	\$10.00
<a href="#">DN-LTS</a>	S	100	\$10.00
<a href="#">DN-LTT</a>	T	100	\$10.00
<a href="#">DN-LTU</a>	U	100	\$10.00
<a href="#">DN-LTV</a>	V	100	\$10.00
<a href="#">DN-LTW</a>	W	100	\$10.00
<a href="#">DN-LTX</a>	X	100	\$10.00
<a href="#">DN-LTY</a>	Y	100	\$10.00
<a href="#">DN-LTZ</a>	Z	100	\$10.00
<a href="#">DN-LTGND</a>	⊕	100	\$10.00
<a href="#">DN-LTPOS</a>	+	100	\$10.00
<a href="#">DN-LTNEG</a>	-	100	\$10.00
<a href="#">DN-LTAC</a>	~	100	\$10.00
<a href="#">DN-LTDC</a>	=	100	\$10.00




- These marking tags allow the flexibility of creating custom marking sequences on site.
- The DN-M series supports a maximum of three digits (tags), while other DINnectors support up to four digits (tags).
- Material: Thermoplastic with heat embossed black print.

**DN-MTA marking tag adapter**



**DN-MTA dimensions**



Part Number	Description	Qty	Price
<a href="#">DN-MTA</a>	Marking tag adapter holds up to six DN-LT tags	50	\$14.50

Note: [DN-MTA](#) adapter does not fit [DN-T12-A](#) terminal blocks.

# DINnectors® Accessories

## Terminal Marking Accessories



**DN-EMLBL1**



**DN-EMLBL2**



**DN-EMLBL3**

Part Number	Description	For Use With	Qty	Price
<b>DN-EMLBL1</b>	Blank labels	DN-EMPEG1 pin protectors for DN-xEMxx plug-in terminal blocks	100	\$9.25
<b>DN-EMLBL2</b>	Labels printed 1 – 12		100	\$13.00
<b>DN-EMLBL3</b>	Labels printed 13 – 24		100	\$13.00

## Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink

Part Number	Description	Qty	Price
<b>DN-MP</b>	Staedtler-Mars marking pen, for use with blank marking tags. Permanent Ink, fine tip.	1	\$4.50



**Marking pen**

## Wire Marking Accessories



**DN-WMTAG1 wire tags & DN-WM-x wire tag holders**

Part Number	Description	For Use With	Qty	Price
<b>DN-WMTAG1</b>	Wire tag – blank	all DN-WM-x wire tag holders	525	\$60.00
<b>DN-WM-1</b>	Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire	<b>DN-WMTAG1</b>	200	\$12.50
<b>DN-WM-2</b>	Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16–11 AWG wire		200	\$12.50
<b>DN-WM-3</b>	Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire		100	\$8.25
<b>DN-WM-4</b>	Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire		100	\$7.75