

VFAS3-4200KPC Cut Sheet



Toshiba AS3 series AC high-performance drive, open frame, 460 VAC, 300hp with 3-phase input, V/Hz, FOC, encoder or torque mode, A8 frame, Ethernet and RS-485, external dynamic braking unit required. Optional EtherCAT, encoder and I/O cards available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFAS3-4200KPC>

Technical Specifications

Brand	Toshiba
Item	Drive
Controller Type	High-performance
Series	AS3
Voltage Type	AC
Nominal Drive Input Voltage	460 VAC
Nominal Drive Output Voltage	460 VAC
Number of Input Phases	3
Number of Output Phases	3
Horsepower By Input Phase	300hp with 3-phase input
Amperage Rating	387A
Variable Torque Amperage Rating	481A
Control Mode	V/Hz, FOC, encoder or torque
Safe Torque Off (STO)	Yes
Temperature Rating	-10 to 50 deg C
Enclosure Type	Open frame
IP Rating	IP00
Mounting	Panel or wall
Frame Size	A8
Dynamic Braking	External dynamic braking unit required
Communication Port and Connection Type(s)	<ul style="list-style-type: none"> • (2) Ethernet (RJ45) • (1) RS-485 (RJ45)
Port Protocol(s)	<ul style="list-style-type: none"> • EtherNet/IP • webserver (non-secure HTTP) • Modbus RTU Slave • Modbus TCP
Port Speed(s)	<ul style="list-style-type: none"> • 10/100 Mbps • up to 38.4k baud
Input Signal	4-20 mA, voltage, potentiometer or pulse train input
Output Type	PWM output
Reverse Capability	Built-in
Internally Bypassed	No

Carrier Frequency Range	1-8 kHz
Output Frequency Range	0.1-590 Hz
Number of Analog Input Channels	3
Number Of Input Channels	3
Analog Input Signal Type	Current/voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	3
Input Resolution	11-bit
Input Current Signal Range	Input current signal range(s) of 0-20 mA, 4-20 mA
Input Voltage Signal Range	Input voltage signal range(s) of +/- 10 VDC
Number of Analog Output Channels	2
Number Of Output Channels	2
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	2
Output Resolution	10-bit
Output Current Signal Range	0-20 mA and 4-20 mA
Output Voltage Signal Range	0-10 VDC
Number of Discrete Input Points	8
Nominal Discrete Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	4

VFAS3-4200KPC Cut Sheet

Number of Discrete Output Points	3
Nominal Discrete Output Voltage	250 VAC and 30 VDC
Discrete Output Type	Relay
Relay Configuration	(1) Form C (SPDT) relay, (2) Form A (SPST) relays
Number of Isolated Discrete Output Commons	3
Number of Points per Discrete Output Common	1
Load Current	2A/point relay
Fuse Type	User-supplied external fuse
Programming Language	User sequence
SCCR Rating	18kA SCCR
Connector Type	Screw terminals
For Use With	3-phase induction and permanent magnet AC motors
Includes	DC reactor (attached) and EMC filter (built-in)
Additional Information	Optional EtherCAT, encoder and I/O cards available.
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.06• Replacement Battery: D0-MC-BAT• Generic Battery: CR2032

Agency Approvals

UL Listed File #	E204788
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	231252
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VFAS3-4200KPC.pdf>
See store item page for other formats.