


VFK1-A0-2M Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 18mm diameter x 70mm body, 316L stainless steel housing, N.O. output, 12mm sensing distance, non-flush, 25 Hz (AC)/300 Hz (DC) switching frequency, IP68 IP69K, 1/2in - 20UNF thread.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFK1-A0-2M>

Technical Specifications

Brand	AutomationDirect
Item	Proximity sensor
Sensor Type	Inductive
Application	Food and beverage and AC powered
Shape	Tubular
Housing Size	18mm diameter x 70mm body
Housing Material	316L stainless steel
Barrel Type	Threaded
Sensing Method	Standard sensing
Adjustable	No
Number of Wires	2
Operation Mode	N.O. output
Sensing Distance	12mm

Mounting Type	Non-flush
IO-Link Compatible	No
Switching Frequency	25 Hz (AC)/300 Hz (DC)
Operating Voltage	20-140 VAC/VDC
Operating Temperature	0 to 100C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP68 IP69K
Connection	1/2in - 20UNF thread
Includes	Mounting hardware
Additional Information	Purchase cable separately. For harsh duty / food and beverage applications

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/VFK1-A0-2M.pdf>
See store item page for other formats.