

VFS75-26-1002 Cut Sheet



ProSense liquid flow sensor, vortex, 3/4in female NPT process connection, 1.3 to 26.4 GPM, 80 to 1585 GPH, 14 to 194 deg F, Output: analog, Output 2: analog, 18 to 30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFS75-26-1002>

Technical Specifications

Brand	ProSense
Item	Flow sensor
Media Type	Liquid
Sensing Type	Vortex
Process Connection	3/4in female NPT
Measuring Range	1.3 to 26.4 GPM
Measuring Range 2	80 to 1585 GPH
Measuring Range 3	14 to 194 deg F
Output	Analog, 4-20 mA
Output 2	Analog, 4-20 mA
Operating Voltage	18 to 30 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document