



Ecoline Enclosure LED Lights Magnet, Clip or Screw Mounted



Magnet Mount



Screw Mount



Clip Mount

Applications

- Suitable for all types of panels and enclosures, especially where space is at a premium
- Suitable for daisy-chaining
- Allows for up to 10 lights to be connected to each other
- No special cables or connectors needed, just connect your wiring to the 2-pole dual cage clamps



Features

- Energy saving LED technology
- Available with magnet, clip, or screw mounts allowing them to be easily positioned in any enclosure.
- Magnet mount has powerful non-slip rubberized magnets and work on ferrous steel only
- Clip mount has specifically designed clip holders for clip mount of the LED 025. The light is snapped into the clip holders and can be rotated 180°.
- Wide voltage range.
- Dual cage clamp for quick wiring.

Listings

- UL File No. E234324
- CE, VDE, EAC

Ecoline Enclosure LED Lights							
Magnet Mount	Price	Screw Mount	Price	Clip Mount	Price	Operating Voltage	Switch Type
025403-10	\$60.00	025403-11	\$49.50	025403-13	\$49.50	AC 100 - 240V, 50/60 Hz (min. 90V, max. 265V) DC 90 - 110V (min. 80V, max. 125V)	On/Off
025413-10	\$115.00	025413-11	\$105.00	025413-13	\$105.00	AC 100 - 240V, 50/60 Hz (min. 90V, max. 265V) DC 90 - 110V (min. 80V, max. 125V)	PIR motion sensor
025423-10	\$58.00	025423-11	\$48.50	025423-13	\$48.50	AC 100 - 240V, 50/60 Hz (min. 90V, max. 265V) DC 90 - 110V (min. 80V, max. 125V)	N/A
025401-10	\$79.00	025401-11	\$69.00	025401-13	\$69.00	DC 24-48 (min. 20V, max. 60V)	On/Off switch
025411-10	\$145.00	025411-11	\$135.00	025411-13	\$135.00	DC 24-48 (min. 20V, max. 60V)	PIR motion sensor
025421-10	\$77.00	025421-11	\$67.00	025421-13	\$67.00	DC 24-48 (min. 20V, max. 60V)	N/A

Ecoline Enclosure LED Lights Specifications	
Power Consumption	Max. 5W (~75 W incandescent bulb)
Luminosity	400 Lm at 120° (1,200 Lm at 360° or equivalent 95 W light bulb)
Lamp Type	LED, 120° angle of radiation light color – daylight, color temperature – 6,000 to 7,000 K
Service Life	60,000 hrs. at 68°F [20°C]
Connection	2-pole dual cage clamp for 14 AWG [2.5 mm ²] solid wire and 16 AWG [1.5 mm ²] stranded wire wire end ferrule
Housing	plastic, transparent
Mounting	Magnet mount Screw mount (M5 screws not included) Clip mount (M6 screws not included)
Operating / Storage Temperature	-22 to 140°F [-30 to 60°C] / -40 to 185°F [-40 to 85°C]
Operating / Storage Humidity	max. 90% RH (non-condensing)
Protection Class	II (double insulated)
Protection Type	IP20
Approvals	CE, UL Recognized File No.: E234324, VDE, EAC, RoHS 2 compliant
Weight	approx. 7 oz. [200 g]




Connection End




Ecoline Enclosure LED Lights Magnet, Clip or Screw Mounted

Dimensions


in [mm]



Magnet Mount



Clip Mount



Screw Mount

Please see our website www.AutomationDirect.com for complete engineering drawings.