


# WG-206-015-D Cut Sheet



IronHorse heavy duty worm gearbox, 15:1 ratio, NEMA 56C input, dual, 1in diameter output shaft, nominal 2.09 hp at 1.0 SF, 1002 lb-in mechanical output torque, 2-1/16in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-206-015-D>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Gearbox
<b>Application</b>	General purpose
<b>Duty Rating</b>	Heavy duty
<b>Gearbox Type</b>	Worm
<b>Gear Ratio</b>	15:1
<b>Speed Rating</b>	1750 rpm input / 117 rpm output
<b>Input Configuration</b>	NEMA 56C
<b>Input Power Rating</b>	Nominal 2.09 hp at 1.0 SF
<b>Output Configuration</b>	Dual

<b>Gearbox Output Shaft Diameter</b>	1in
<b>Mechanical Output Torque</b>	1002 lb-in
<b>Thermal Output Torque</b>	673 lb-in
<b>Center Distance</b>	2-1/16in
<b>Housing Material</b>	Cast iron
<b>Mounting</b>	Tapped-base
<b>Finish</b>	Anti-corrosion primer and paint
<b>Lubrication Type</b>	Pre-filled with synthetic lube
<b>Oil Seal Type</b>	Double-lip

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/WG-206-015-D.pdf>  
See store item page for other formats.