

# Cross Reference Guide



| <b>CROSS REFERENCE GUIDE By manufacturers type reference or series number.<br/>Ampere ratings must be added for ordering purposes.</b> |                         |             |                           |                          |                 |                          |                  |                   |
|--|-------------------------|-------------|---------------------------|--------------------------|-----------------|--------------------------|------------------|-------------------|
| <b>FUSE TYPE</b>   |                         | <b>VOLT</b> | <b>EDISON</b>             | <b>BRUSH/<br/>DORMAN</b> | <b>BUSSMANN</b> | <b>MERSEN/<br/>GOULD</b> | <b>GEC/CEFCO</b> | <b>LITTELFUSE</b> |
| <b>UL CLASS CURRENT LIMITING FUSES (CSA CLASS)</b>   |                         |             |                           |                          |                 |                          |                  |                   |
| CC (HRCl-CC)   | Time-Delay              | 600         | EDCC                      | –                        | LP-CC           | ATDR                     | –                | CCMR              |
|  | Time-Delay              | 600         | HCTR                      | –                        | FNQ-R           | ATQR                     | –                | KLDR              |
|  | Fast-Acting             | 600         | HCLR                      | HCLR                     | KTK-R           | ATMR                     | CTK-R            | KLKR              |
| RK1  | Time-Delay Dual Element | 250         | LENRK                     | –                        | LPN-RK-SP       | A2DR                     | –                | LLNRK             |
|  |                         | 600         | LESRK                     | –                        | LPS-RK-SP       | A6DR                     | –                | LLSRK             |
| RK5  | Time-Delay Dual Element | 250         | ECNR                      | –                        | FRN-R           | TR                       | –                | FLNR              |
|  |                         | 600         | ECSR                      | –                        | FRS-R           | TRS                      | –                | FLSR              |
| J  | Time-Delay Dual Element | 600         | JDL                       | –                        | LPJ             | AJT                      | –                | JTD               |
|  | High-Speed AC Drive     | 600         | JHL                       | –                        | DFJ             | HSJ                      | –                | –                 |
| T  | Extremely Fast-Acting   | 300         | TJN                       | –                        | JJN             | A3T                      | –                | JLLN              |
|  |                         | 600         | TJS                       | –                        | JJS             | A6T                      | –                | JLLS              |
| <b>UL CLASS GENERAL PURPOSE FUSES</b>  |                         |             |                           |                          |                 |                          |                  |                   |
| Midget   | Fast-Acting             | 600         | MCL                       | MCL                      | KTK             | ATM                      | CTK              | KLK               |
|  |                         | 250         | MOL                       | MOL                      | BAF/BAN         | OTM                      | –                | BLF               |
|  | Time-Delay              | 500         | MEQ                       | MEQ                      | FNQ             | ATQ                      | –                | FLQ               |
|  |                         | 250         | MEN                       | MEN                      | FNM             | TRM                      | –                | FLM               |
| 1/4" x 1-1/4" Ceramic  | Fast-Acting             | 250/125     | ABC                       | ABC                      | ABC             | GAB                      | –                | 314               |
| 1/4" x 1-1/4" Glass  |                         | 250/32      | AGC                       | AGC                      | AGC             | GGC                      | –                | 312               |
| 1/4" x 1-1/4" Ceramic  | Time-Delay              | 250         | MDA                       | MDA                      | MDA             | –                        | –                | 326               |
| 1/4" x 1-1/4" Glass  |                         | 250/32      | MDL                       | MDL                      | MDL             | GDL                      | –                | 313               |
| 5x20 mm Glass  | Fast-Acting             | 250/125     | GMA                       | GMA                      | GMA             | GGM                      | –                | 235               |
|  | Medium Time-Delay       | 250/125     | GMC                       | GMC                      | GMC             | GSC                      | –                | –                 |
| 5x20 mm Glass  | Fast-Acting             | 250         | S500                      | BDB                      | GDB             | GSB                      | –                | 217               |
|  | Time-Delay              | 250         | S506                      | BDC                      | GDC             | GDG                      | –                | 218               |
| <b>Fuse Puller</b>   |                         |             |                           |                          |                 |                          |                  |                   |
| Fuse Puller FP-2   |                         | –           | old - 38072<br>new - FP-2 | –                        | FP-2            | –                        | –                | –                 |