


WSK-A0-3E Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 18mm diameter x 40mm body, weld coated 316 stainless steel housing, NPN/PNP, N.O. output, 6mm sensing distance, flush, 50 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WSK-A0-3E>

Technical Specifications

Brand	AutomationDirect	Mounting Type	Flush
Item	Proximity sensor	Switching Frequency	50 Hz
Sensor Type	Inductive	Operating Voltage	10–36 VDC
Application	Welding	Operating Temperature	-25 to +70 °C
Shape	Tubular	Weld Field Immune	No
Housing Size	18mm diameter x 40mm body	Chip Immune	No
Housing Material	Weld coated 316 stainless steel	IP Rating	IP67
Barrel Type	Threaded	Connection	4-pin M12 quick-disconnect
Sensing Method	Extended sensing	IO-Link Compatible	No
Adjustable	No	Cable Length	0.9ft/0.3m
Number of Wires	2	Jacket Material	PVC
Switching Output	NPN/PNP	Includes	Mounting hardware
Operation Mode	N.O. output	Additional Information	Purchase cable separately
Sensing Distance	6mm		

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WSK-A0-3E.pdf>
See store item page for other formats.