



# Enclosure Air Conditioners


## Applications

Designed to maintain the temperature inside an electrical enclosure at or below a safe level for the enclosed equipment, while maintaining a closed loop environment inside the enclosure to keep out contaminants that can be in the ambient air. Can be used in environments such as steel, food processing, petro-chemical, cement, paper/pulp and plastics industries, provided there are no corrosive gases or liquids that could damage internal components.

## Construction

- Free-standing rigid chassis for easy installation and maintenance
- All mounting hardware, full-size template and instruction manual included
- Power input terminal block on all models
- All Type 4 and 4x models come with condenser coils coated with an electrically applied corrosion-resistant coating

## Features

- Programmable temperature controller with visible alarm features in a 0.57 x 0.29 in [14.5 x 7.3 mm] panel
- 60 °F to 95 °F (20 °C to 35 °C) temperature control range
- 50 °F to 125 °F (10 °C to 52 °C) ambient temperature range
- Pre-wired for external alarm monitoring connections (22 AWG three-conductor cable, 7ft (2.3 m) long)
- Active condensate evaporation system with safety overflow
- Protective coated condenser coils on NEMA Type 4 and 4X for corrosion resistance.
- Thermal expansion valve for maximum efficiency over wide range of temperatures and loads
- Anti short-cycle compressor protection
- High and low refrigerant cut-outs with fault indication
- Highly energy-efficient compressors 
- UL/cUL listed



TA10-060-26-12 shown

Stratus Air Conditioners General Specifications

Part Number	Nominal Cooling Capacity (BTU/H)	Operating Voltage	Inrush Current (A)	Running Current (A)	Recommended Fuse Size/ Time Delay (A)	SCCR (A)	Connection	Refrigerant	Refrigerant Amount (oz)			
TA10-010-16-xx	1000	120VAC/60Hz	14.50	2.69	12	*	Spring cage terminal block 24-8 AWG	R134a	4.00			
TA10-010-26-xx		230VAC/60Hz	14.00	1.99	7	*						
TA20-010-48D-xx		48VDC	-	3.70	8 (fast acting)	*						
TA20-010-16-xx	120VAC/60Hz	10.10	2.70	5	*							
TA10-015-16-xx	1500	120VAC/60Hz	14.60	3.44	12	*		Spring cage terminal block 24-8 AWG	R134a	7.75		
TA10-015-26-xx		230VAC/60Hz	13.30	2.67	7	*						
TA20-020-16-xx	2000	120VAC/60Hz	10.63	3.36	5	*			Spring cage terminal block 24-8 AWG	R134a	12.00	
TA20-020-26-xx		230VAC/60Hz	8.84	2.00	4	*						
TA10-020-16-xx		120VAC/60Hz	23.42	5.15	12	*						
TA10-020-26-xx	230VAC/60Hz	13.65	3.07	7	*	Spring cage terminal block 16-6 AWG				R422d	10.25	
TA10-020-46-xx	480VAC/60Hz	5.86	1.51	3	160kA							
TA10-040-16-xx	4000	120VAC/60Hz	16.42	3.76	8		*					Spring cage terminal block 16-6 AWG
TA10-040-26-xx		230VAC/60Hz	13.41	3.07	6		*					
TA10-040-46-xx		480VAC/60Hz	4.11	0.93	2		160kA					
TA10-050-16-xx	5000	120VAC/60Hz	23.42	7.26	12		*	Spring cage terminal block 16-6 AWG		R422d	12.50	
TA10-050-26-xx		230VAC/60Hz	19.15	3.76	10		*					
TA10-050-46-xx		480VAC/60Hz	9.18	1.44	5		160kA					
TA10-060-16-xx	6000	120VAC/60Hz	42.41	7.83	25		*		Spring cage terminal block 16-6 AWG	R422d	18.00	
TA10-060-26-xx		230VAC/60Hz	21.15	4.80	12		*					
TA10-060-46-xx		480VAC/60Hz	10.13	1.80	5	160kA						

\*SCCR rating is based on the SCCR rating for the circuit protection device installed in the panel/enclosure per UL484 & UL484a to protect the AC unit. Typically, 100kA - 200kA for Time-Delay Fuses. Atmosphere: No corrosive gases or liquids.



# TA10 Series Enclosure Air Conditioners, Frame Size TA10-3

## NEMA 12 Construction

- Fabricated from 16-gauge cold rolled steel
- ANSI-61 gray polyester powder coating inside and out
- Pre-cut mounting gasket included, to be field installed
- All mounting hardware, full-size template and instruction manual included
- Power input terminal block on all models

## NEMA 4 Construction

- Fabricated from 16-gauge cold rolled steel
- ANSI-61 gray polyester powder coating inside and out
- Pre-cut mounting gasket installed for NEMA/UL type rating on all units
- All mounting hardware, full-size template and instruction manual included
- Power input terminal block on all models

## NEMA 4X Construction

- Fabricated from 16-gauge 304 stainless steel
- Pre-cut mounting gasket installed for NEMA/UL type rating on all units
- All mounting hardware, full-size template and instruction manual included
- Power input terminal block on all models

## Features

- Fits 12in deep enclosures that have smooth/flat sides. Check enclosure dimensions/specifications before ordering.
- Protective coated condenser coils on NEMA Type 4 and 4X for corrosion resistance.

## Listings

- UL File: SA33404
- UL 50, Type 12, 4, and 4X
- Made in USA



TA10-050-16-4X

TA10 Enclosure Air Conditioners, Frame Size TA10-3								
NEMA 12	Price	NEMA 4	Price	NEMA 4X	Price	Nominal Cooling Capacity (BTU/H)	Operating Voltage	Weight (lb)
TA10-050-16-12	\$2,209.00	TA10-050-16-04	\$2,489.00	TA10-050-16-4X	\$3,087.00	5000	120VAC/60Hz	89
TA10-050-26-12	\$2,254.00	TA10-050-26-04	\$2,534.00	TA10-050-26-4X	\$3,132.00		230VAC/60Hz	89
TA10-050-46-12	\$2,848.00	TA10-050-46-04	\$3,128.00	TA10-050-46-4X	\$3,726.00		480VAC/60Hz	132
TA10-060-16-12	\$2,476.00	TA10-060-16-04	\$2,756.00	TA10-060-16-4X	\$3,354.00	6000	120VAC/60Hz	96
TA10-060-26-12	\$2,521.00	TA10-060-26-04	\$2,798.00	TA10-060-26-4X	\$3,398.00		230VAC/60Hz	96
TA10-060-46-12	\$3,353.00	TA10-060-46-04	\$3,633.00	TA10-060-46-4X	\$4,231.00		480VAC/60Hz	139


\* Voltage variation no greater than ± 10% from nameplate rating and Frequency variation no greater than ± 3Hz from nameplate rating.




# TA10 Series Enclosure Air Conditioners, Frame Size TA10-3

## Air Conditioner Performance Curves


TA10-050-16-xx




TA10-050-26-xx  
TA10-050-46-xx



TA10-060-16-xx




TA10-060-26-xx  
TA10-060-46-xx



## Air Conditioner Dimensions

Dimensions in inches [millimeters]



SEE OUR WEBSITE: [WWW.AUTOMATIONDIRECT.COM](http://WWW.AUTOMATIONDIRECT.COM) FOR COMPLETE ENGINEERING DRAWINGS.



# Air Conditioners Filters

## Replacement Filters

Replacement filters are identical to the original filters supplied with the air conditioners. Clean/replace the filter regularly to keep the air conditioner working at its highest efficiency.

### Features

- 250 micron expanded aluminum filter element
- 60% filter efficiency
- Washable and reusable



TA10-FILTER-3







TA20-FILTER-1

Air Conditioner Filters			
Part Number	Price	Description	Frame Size
TA10-FILTER-1	\$24.00	Replacement filter for TA10 series air conditioning units, 1000 to 1500 BTU/H	TA10-1
TA10-FILTER-2	\$26.00	Replacement filter for TA10 series air conditioning units, 2000 to 4000 BTU/H	TA10-2
TA10-FILTER-3	\$29.00	Replacement filter for TA10 series air conditioning units, 5000 to 6000 BTU/H	TA10-3
TA20-FILTER-1	\$27.00	Replacement filter for TA20 series air conditioning units, 2000 BTU/H	TA20-1

### Dimensions

Dimensions in inches [millimeters]





# 2" Louvered Frame and Filter Kits

2-inch louvered frame and filter kits are ideal in food processing or dirty environments where filter maintenance is crucial. Stratus offers extended surface, 2-inch deep filter and sliding filter frame assemblies. In wash-down applications, stainless steel filters are preferred over aluminum filters.

## Features

- 2in louvered frame and filter kit
- 250 micron stainless steel mesh filter
- 97% efficiency extends filter capacity 400%
- Washable and reusable
- Deep filter frames easily retrofitted on existing units with standard filters using the same mounting hole and screws on your unit






TA20-LVFL-1-4X

Air Conditioner Filters			
Part Number	Price	Description	Frame Size
TA10-LVFIL-2-04	\$315.00	Stratus louvered filter frame assembly, carbon steel, ANSI 61 gray finish, with filter, washable, 2in filter depth, 250 micron stainless steel mesh, 97% filter efficiency. For use with 2000-4000 BTU/H TA10 series enclosure air conditioners on NEMA 4 or NEMA 12 enclosures.	TA10-2
TA10-LVFIL-3-04	\$342.00	Stratus louvered filter frame assembly, carbon steel, ANSI 61 gray finish, with filter, washable, 2in filter depth, 250 micron stainless steel mesh, 97% filter efficiency. For use with 5000-6000 BTU/H TA10 series enclosure air conditioners on NEMA 4 or NEMA 12 enclosures.	TA10-3
TA10-LVFIL-2-4X	\$325.00	Stratus louvered filter frame assembly, 304 stainless steel, with filter, washable, 2in filter depth, 250 micron stainless steel mesh, 97% filter efficiency. For use with 2000-4000 BTU/H TA10 series enclosure air conditioners on NEMA 4X enclosures.	TA10-2
TA10-LVFIL-3-4X	\$360.00	Stratus louvered filter frame assembly, 304 stainless steel, with filter, washable, 2in filter depth, 250 micron stainless steel mesh, 97% filter efficiency. For use with 5000-6000 BTU/H TA10 series enclosure air conditioners on NEMA 4X enclosures.	TA10-3
TA20-LVFIL-1-04	\$242.00	Stratus louvered filter frame assembly, carbon steel, ANSI 61 gray finish, with filter, washable, 2in filter depth, 250 micron stainless steel mesh, 97% filter efficiency. For use with 2000 BTU/H TA20 series enclosure air conditioners on NEMA 4 or NEMA 12 enclosures.	TA20-1
TA20-LVFIL-1-4X	\$249.00	Stratus louvered filter frame assembly, 304 stainless steel, with filter, washable, 2in filter depth, 250 micron stainless steel mesh, 97% filter efficiency. For use with 2000 BTU/H TA20 series enclosure air conditioners on NEMA 4X enclosures.	TA20-1

## Dimensions

Dimensions in inches [millimeters]



# Industrial strength cooling options for your enclosure from AutomationDirect



- Both intake (FPI) and exhaust (FPO) fans are available.
- Exhaust fans and grilles available with air flaps or filters. Using air flaps on the exhaust reduces the number of filters to maintain.



## Filter Fan Kits

- Easy filter change
- Outer door lock for outdoor models
- Impact resistant
- Weather/UV resistant -f1
- Flammability Rating: UL94V-0
- Adhesive mounting for non-screw installation (except outdoor models)
- Low noise
- 120VAC and 24VDC models available

## Filter Fan Plus

- Easy filter change
- Hinged cover
- Impact resistant
- Weather/UV resistant-UL-f1
- Flammability Rating: UL94V-0
- Unique ratchet mechanism for no-screw installation
- Low noise
- 120, 230VAC and 12, 24, 48VDC models available

## Hose-Proof Filter Fan Hoods

- Stainless steel hood with food-grade silicone seal
- Fits all Stego Filter Fan and Filter Fan Plus fans and exhaust grilles (except outdoor Filter Fans)
- Maintains an enclosure's NEMA/UL Type 4 or 4X rating in washdown environments



## Fan Kits



- All models are 115V with an expected service life of 30,000 hours
- High-performance fan motors and finger guards
- Polycarbonate fire retardant plastic grilles, UL94-V0
- Durable, reusable filter mat included
- Patented "Click and Fit" system allows for rapid filter fan and exhaust filter installation without screws



# Industrial strength cooling options for your enclosure from AutomationDirect



## Heat Exchangers

- For NEMA 4 and 4X enclosures
- Closed loop cooling
- Energy efficient: uses approximately the same power as a filtered fan system
- 120VAC and 24VDC models available

---

## Air Conditioning Units

- For NEMA 12, 4, 4X type enclosures
- Digital temperature controller
- Active condensate evaporation system
- High unit efficiency
- Tough industrial construction
- Compressor protection system



Made  
in the  
USA



---

## Enclosure Vortex Coolers



- For NEMA 12, 4, 4X type enclosures
- Operates on compressed air
- Stainless steel construction
- No moving parts, no maintenance required
- Vortex coolers can be “resized” for changing applications by simply replacing the generator inside the cooler. No need to purchase a new unit
- Replacing the vortex generator takes minutes