


# WSM-A0-3E Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 12mm diameter x 40mm body, weld coated 316 stainless steel housing, NPN/PNP, N.O. output, 4mm sensing distance, flush, 75 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WSM-A0-3E>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Inductive
<b>Application</b>	Welding
<b>Shape</b>	Tubular
<b>Housing Size</b>	12mm diameter x 40mm body
<b>Housing Material</b>	Weld coated 316 stainless steel
<b>Barrel Type</b>	Threaded
<b>Sensing Method</b>	Extended sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	2
<b>Switching Output</b>	NPN/PNP
<b>Operation Mode</b>	N.O. output
<b>Sensing Distance</b>	4mm

<b>Mounting Type</b>	Flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	75 Hz
<b>Operating Voltage</b>	10-36 VDC
<b>Operating Temperature</b>	-25 to 70c
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP67
<b>Connection</b>	4-pin M12 quick-disconnect
<b>Cable Length</b>	0.9ft/0.3m
<b>Jacket Material</b>	PVC
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>