

XBF-LD02S Cut Sheet



LS Electric XGB load cell input module, 2-channel, voltage, 15-bit resolution, input voltage signal range(s) of 0-6 mV/VDC. For use with 5 VDC four- or six-wire load cells. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XBF-LD02S>

Technical Specifications

Brand	LS Electric XGB
Item	Input module
I/O Module Type	Load cell
Number Of Input Channels	2
Input Signal Type(s)	Voltage
Isolated Channels	Yes
Input Resolution	15-bit
Input Voltage Signal Range	0-6 mV/VDC
External Power Requirement	External 24 VDC required
Sample Rate	5ms
For Use With	5 VDC four- or six-wire load cells
Includes	Removable terminal blocks
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XBF-LD02S.pdf>
See store item page for other formats.