


# XTH2-0-UNV-P Cut Sheet



ProSense programmable temperature transmitter, isolated, RTD, thermocouple, millivolt or potentiometer input, deg F or deg C, current output, 10-36 VDC operating voltage, DIN Form B connection head mount, push-in terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTH2-0-UNV-P>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Programmable temperature transmitter
<b>Isolation</b>	Isolated
<b>Field Configurable</b>	Yes
<b>Input Potentiometer Resistance</b>	10-2000 Ohms
<b>Input RTD Signal Types</b>	Cu50, Cu100, Ni100, Ni120, Pt100, Pt200, Pt500 and Pt1000
<b>Input Thermocouple Signal Type</b>	J, K, L, N, R, S, T, U, A, B, C, D, E
<b>Input Voltage Signal Range</b>	-20 to 100 mV
<b>Programmable Temperature Range</b>	Deg F or deg C
<b>Output Current Signal Range</b>	4-20 mA and 20-4 mA
<b>Operating Voltage</b>	10-36 VDC
<b>Housing Material</b>	Polycarbonate
<b>Mounting</b>	DIN Form B connection head
<b>Electrical Connection</b>	Push-in terminals
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	601711
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>