


XTOE045CCSS Cut Sheet



Eaton XT series electronic overload relay, 9.0-45.0A adjustable, solid state, local reset, stand-alone power connection(s), DIN rail or panel mount. For use with any contactor.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTOE045CCSS>

Technical Specifications

Brand	Eaton
Item	Relay
Series	XT
Relay Type	Electronic overload
Full Load Amperage Range	9.0-45.0A adjustable
Operation Type	Solid state
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Selectable 10A/10/20/30

Reset	Local
Phase Loss Sensitive	Yes
Ground Fault Protection	No
Connection	Stand-alone power
Mounting	DIN rail or panel
For Use With	Any contactor
Additional Information	Self powered, selectable phase imbalance protection, optional communications available

Agency Approvals

UL Listed File #	E1230
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	156828, 000353_0_000
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XTOE045CCSS.pdf>
See store item page for other formats.