


# Magnetic Pulse Input Module



## Overview

The F4-8MPI is an eight-channel Magnetic Pulse Input CoProcessor Module. It is designed to take input pulses from Hall effect type magnetic pickups, (typically found on turbine meters, tachometers and signal generators), and perform calculations. Up to eight differential inputs from magnetic pickups are wired directly to the terminal block on the front of the module.

The Magnetic Pulse module is based on the FACTS Engineering CoProcessor design. Therefore, it offers a built-in real-time battery-backed clock/calendar and a very fast floating point processor. Because of this powerful design, it can easily support Indicated Volume, Gross Volume, Volume Logging, Flow rate, and Tachometer modes. These operational modes are explained in the adjacent chart.



Specifications	
<b>Module Type</b>	CoProcessor, Intelligent
<b>Number of Channels</b>	Eight Differential per module
<b>Modules per CPU</b>	Eight Maximum, any slot in CPU base
<b>Input Voltage Range</b>	±10mV to ±10VDC peak
<b>Input Frequency Range</b>	DC to 5.0 kHz (channels 1 to 4) DC to 2.5 kHz (channel 5 to 8)
<b>Maximum Continuous Overload</b>	-150 to +150VDC, 220 Vrms
<b>Input Impedance</b>	100KΩ
<b>Differential Low – Pass Filter</b>	f <sub>-3db</sub> = 20kHz, 6db per octave roll-off
<b>Common Mode Voltage Range</b>	±15VDC
<b>Common Mode Rejection</b>	Over common mode input voltage range
<b>Update Time</b>	3 PLC scans minimum
<b>Isolation</b>	750VDC, channels to PLC
<b>LED Status Indicators</b>	Power ON, Input Pulse (8 LEDs)
<b>Field Termination</b>	20 position removable terminal block 16 positions, ±CHn, Pulse inputs 2 positions, 24VDC power supply
<b>External Power Required</b>	170mA maximum, +18 to +25VDC
<b>Internal Power Consumption</b>	225mA from 5VDC maximum
<b>External Power Required</b>	170mA maximum, +18 to +25VDC
<b>Internal Power Consumption</b>	225mA from 5VDC maximum
<b>Operating Environment</b>	0°C to 60°C (32°F to 140°F)/5% to 95% humidity (non-condensing)

Modes	
<b>Indicated and Gross Volume</b>	
<b>Configuration</b>	The module calculates Indicated Volume of flow given a K Factor. The K Factor is the nominal pulses per unit for the flow meter. This is the factory calibration number normally stamped on the flow meter housing. Indicated volume may be in pulses, gallons, dm <sup>3</sup> , or barrels depending on the K Factor. Gross Volume may also be calculated by substituting for the K Factor, the K Factor divided by the Meter Factor (Meter Factor is the calibration factor derived at the installation).
<b>Output Data</b>	Total volume of flow is output to the PLC in engineering units. The formulas used to calculate volume are: Indicated Volume = Total Pulses ÷ K Factor Gross Volume = Total Pulses ÷ (K Factor/Meter Factor)
<b>Flow Rate</b>	
<b>Configuration</b>	The flow rate calculation uses the same configuration information as the Volume calculation. The sample rate may range from .1 to 999.9 seconds, or minutes.
<b>Output Data</b>	Flow rate is output to the PLC in engineering units. The formula used to calculate flow rate is: (Volume last sample time – Current Volume) ÷ Sample Rate.
<b>Volume Logging</b>	
<b>Configuration</b>	Indicated or gross volume may be logged at either a particular time or at periodic intervals throughout the day. If desired, the counters may be automatically reset when the data is logged. The built-in real time battery-backed clock calendar must be set before volume logging is enabled.
<b>Output Data</b>	Indicated or gross volume is output to the PLC in engineering units. A one-shot flag is also set to indicate to the PLC that new data has been logged.
<b>Tachometer</b>	
<b>Configuration</b>	Tachometer applications are simply a variation of the flow rate calculation. To calculate revolutions per minute, set the K Factor equal to the number of pulses per revolution multiplied by 60. Set the Sample Rate equal to one second. To calculate pulses per second (PPS), set the K Factor equal to one and the Sample Rate equal to one second.
<b>Output Data</b>	RPM or PPS

# Check the Power Budget

## Verify your power budget requirements

Your I/O configuration choice can be affected by the power requirements of the I/O modules you choose. When determining the types and quantity of I/O modules you will be using, it is important to remember there is a limited amount of power available from the power supply.

The chart on the opposite page indicates the power supplied and used by each DL405 device. The adjacent chart shows an example of how to calculate the power used by your particular system. These two charts should make it easy for you to determine if the devices you have chosen fit within the power budget of your system configuration.

If the I/O you have chosen exceeds the maximum power available from the power supply, you can resolve the problem by shifting some of the modules to an expansion base or remote I/O base (if you are using remote I/O).

**Warning: It is extremely important to calculate the power budget correctly. If you exceed the power budget, the system may operate in an unpredictable manner which may result in a risk of personal injury or equipment damage.**

## Use ZIPLinks to reduce power requirements

If your application requires a lot of relay outputs, consider using the ZIPLink AC or DC relay output modules. These modules can switch high current (10A) loads without putting a load on your base power budget. Refer to Wiring System for DL405 PLCs later in this section for more information.

This logo is placed next to I/O modules that are supported by the ZIPLink connection systems.

See the I/O module specifications at the end of this section.



## Calculating your power usage

The following example shows how to calculate the power budget for the DL405 system. The example is constructed around a single 8-slot base using the devices shown. It is recommended you construct a similar table for each base in your system.

A				
	<b>Base Number</b> 0	<b>Device Type</b>	<b>5 VDC (mA)</b>	<b>External 24 VDC Power (mA)</b>
<b>B</b>	<b>CURRENT SUPPLIED</b>			
	<b>CPU/Expansion Unit /Remote Slave</b>	D4-454 CPU	3700	400
<b>C</b>	<b>CURRENT REQUIRED</b>			
	<b>SLOT 0</b>	D4-16ND2	+150	+0
	<b>SLOT 1</b>	D4-16ND2	+150	+0
	<b>SLOT 2</b>	F4-04DA	+120	+100
	<b>SLOT 3</b>	D4-08NA	+100	+0
	<b>SLOT 4</b>	D4-08NA	+100	+0
	<b>SLOT 5</b>	D4-16TD2	+100	+0
	<b>SLOT 6</b>	D4-16TD2	+100	+0
	<b>SLOT 7</b>	D4-16TR	+1000	+0
<b>D</b>	<b>OTHER</b>			
	<b>BASE</b>	D4-08B-1	+80	+0
	<b>Handheld Programmer</b>	D4-HPP-1	+320	+0
<b>E</b>	<b>Maximum Current Required</b>		<b>2820</b>	<b>100</b>
<b>F</b>	<b>Remaining Current Available</b>		<b>3700-2820=880</b>	<b>400-100=300</b>
	1. Using a chart similar to the one above, fill in column 2. 2. Using the tables on the opposite page, enter the current supplied and used by each device (columns 3 and 4). Pay special attention to the current supplied by the CPU, Expansion Unit, and Remote Slave since they differ. Devices which fall into the "Other" category (Row D) are devices such as the Base and the Handheld programmer, which also have power requirements, but do not plug directly into the base. 3. Add the current used by the system devices (columns 3 and 4) starting with Slot 0 and put the total in the row labeled "maximum current required" (Row E). 4. Subtract the row labeled "Maximum current required" (Row E), from the row labeled "Current Supplied" (Row B). Place the difference in the row labeled "Remaining Current Available" (Row F). 5. If "Maximum Current Required" is greater than "Current Supplied" in either column 3 or 4, the power budget will be exceeded. It will be unsafe to use this configuration and you will need to restructure your I/O configuration. Note the auxiliary 24VDC power supply does not need to supply all the external power. If you need more than the 400mA supplied, you can add an external 24VDC power supply. This will help keep you within your power budget for external power.			

## DL405 CPU power supply specifications and power requirements

Specification	AC Powered Units	24 VDC Powered Units
<b>Part Numbers</b>	D4-454, D4-EX (expansion base unit), D4-RS (remote slave unit)	D4-454DC-1, D4-EXDC (expansion base unit)
<b>Voltage Withstand (dielectric)</b>	1 minute @ 1,500 VAC between primary, secondary, field ground, and run relay	
<b>Insulation Resistance</b>	> 10MΩ at 500VDC	
<b>Input Voltage Range</b>	85-132 VAC (110V range) 170-264 VAC (220V range)	20-28 VDC (24VDC) with less than 10% ripple
<b>Maximum Inrush Current</b>	20A	20A
<b>Maximum Power</b>	50VA	38W

# Power Requirements

Power Supplied					
<i>CPUs/Remote Units/ Expansion Units</i>	<i>5 VDC Current Supplied in mA</i>	<i>24V Aux Power Supplied in mA</i>	<i>CPUs/Remote Units/ Expansion Units</i>	<i>5V Current Supplied in mA</i>	<i>24V Aux Power Supplied in mA</i>
D4-454 CPU D4-454DC-1	3100 3100	400 NONE	D4-EX D4-EXDC D4-RS H4-EBC	4000 4000 3700 3470	400 NONE 400 400
Power Consumed					
<i>Power-consuming Device</i>	<i>5V Current Consumed</i>	<i>External 24VDC Current Required</i>	<i>Power-consuming Device</i>	<i>5V Current Consumed</i>	<i>External 24VDC Current Required</i>
<i>I/O Bases</i>			<i>Analog Modules (continued)</i>		
D4-04B-1 D4-06B-1 D4-08B-1	80 80 80	NONE NONE NONE	F4-16AD-1 F4-16AD-2 F4-04DA-1 F4-04DA-2 F4-04DAS-1 F4-08DA-1 F4-08DA-2 F4-16DA-1 F4-16DA-2 F4-08RTD F4-08THM-n F4-08THM	75 75 70 90 60 90 80 90 80 80 120 110	100 100 75+20 per circuit 90 60 per circuit 100+20 per circuit 150 100+20 per circuit 25 max. NONE 50 60
<i>DC Input Modules</i>			<i>Remote I/O</i>		
D4-16ND2 D4-16ND2F D4-32ND3-1 D4-64ND2	150 150 150 300 max.	NONE NONE NONE NONE	H4-ERM100 H4-ERM-F D4-RM	320(300) 450 300	NONE NONE NONE
<i>AC Input Modules</i>			<i>Communications and Networking</i>		
D4-08NA D4-16NA	100 150	NONE NONE	H4-ECOM100 D4-DCM F4-MAS-MB	300 500 235	NONE NONE NONE
<i>AC/DC Input Modules</i>			<i>CoProcessors</i>		
D4-16NE3	150	NONE	F4-CP128-1	305	NONE
<i>DC Output Modules</i>			<i>Specialty Modules</i>		
D4-16TD1 D4-16TD2 D4-32TD1 D4-32TD2 D4-64TD1	200 400 250 350 800	125 NONE 140 120 (4A max including loads) NONE	H4-CTRIO D4-INT F4-8MPI D4-16SIM F4-4LTC	400 100 225 150 280	NONE NONE 170 NONE 75
<i>AC Output Modules</i>			<i>Programming</i>		
D4-08TA D4-16TA	250 450	NONE NONE	D4-HPP-1 (Handheld Prog.)	320	NONE
<i>Relay Output Modules</i>			<i>Operator Interface</i>		
D4-08TR F4-08TRS-1 F4-08TRS-2 D4-16TR	550 575 575 1000	NONE NONE NONE NONE	DV-1000 C-more Micro-Graphic	150 210	NONE NONE
<i>Analog Modules</i>					
F4-04AD F4-04ADS F4-08AD	150 370 75	100 120 90			