


FC Series Accessories



FC-5MM



FC-35MM

Description

Universal terminal block replacements for the FC Series signal conditioners. Each package includes enough terminal blocks to replace all the terminal blocks on any FC Series signal conditioner according to the following table:

FC Series Terminal Blocks		
FC Series Model	Terminal Block Replacement Part Number	Package Includes
FC-11	FC-5MM	(2) 2-pole blocks (2) 3-pole blocks (1) 4-pole blocks
FC-33		
FC-R1		
FC-T1		
FC-ISO-C	FC-35MM	(6) 2-pole blocks (2) 3-pole blocks (2) 4-pole blocks (1) 5-pole blocks (1) 6-pole blocks (2) 8-pole blocks
FC-ISO-D		
FC-B34		
FC-35B		
FC-P3		
FC-3RLY2		
FC-3RLY4		

Note: Depending on the model, some terminal blocks in the package may be unused.

Universal Signal Conditioners				
Part No.	Description	Rated Torque (N-m)	Weight (Lbs)	Price
FC-5MM	Terminal block, replacement, 5mm. Package of 5. For use with FC Series signal conditioners.	0.5	0.1	\$10.00
FC-35MM	Terminal block, replacement, 3.5mm. Package of 14. For use with FC Series signal conditioners.	0.2	0.1	\$21.00

FC Series Signal Conditioners



FC-33

DC Selectable Signal Conditioner with 3-way isolation

Field configurable input and output ranges of 0-5V, 0-10 V, 0-20 mA and 4-20 mA with 1500 VDC isolation between input and output, and 1500 VDC isolation from 24 volt power and input/output. LED indicates normal operation and is used in conjunction with the calibration pushbutton for the internal calibration process.

- 3-way 1500 V isolation
- Push button calibration



FC-11

4-20 mA Isolated Signal Conditioner

Loop powered 4-20 mA input/output signal with 1500 VDC isolation between input and output.

- 1500 V isolation
- Loop powered



FC-T1

Thermocouple/mV Isolated Signal Conditioner

Field configurable input for type J, K, E, T, R, S, B, N and C thermocouples or ± 156.25 mV inputs with 1500 VDC isolation between input and the 4-20 mA output. Cold junction compensation and burnout detection. Alarm/run LED.

- 1500 V isolation
- Cold junction compensation (CJC)
- Internal diagnostics (burnout detection or calibration errors)



FC-R1

RTD Input Signal Conditioner

Loop powered, non-isolated, 3-wire unit converts an RTD input to a linear 4-20 mA signal. User selectable CU10, PT100 or PT1000 input.



FC-P3

Potentiometer Input, Analog Output Signal Conditioner

Field configurable input and output, input ranges of 3-wire potentiometer 0 to 100 ohms through 0 to 100 kilohms, and output ranges of 0-5V, 0-10 V, 0-20 mA or 4-20 mA. Field calibrated to 10% of potentiometer full range.



FC-35B

Unipolar Voltage or Current to Bipolar Voltage Signal Conditioner

Field configurable input and output, unipolar input ranges of 0-5V, 0-10 V, 0-20 mA or 4-20 mA, and bipolar output ranges of ± 100 mV, ± 50 mV, ± 5 V, ± 10 V, ± 15 V. Field calibrated with offset and span adjustments.



FC-B34

Bipolar Voltage to Unipolar Voltage or Current Signal Conditioner

Field configurable input and output, bipolar input ranges of ± 100 mV, ± 50 mV, ± 5 V, ± 10 V, ± 15 V, and unipolar output ranges of 0-5V, 0-10 V, 0-20 mA or 4-20 mA. Field calibrated with offset and span adjustments.



FC-3RLY2

Analog Input, 2-Relay, Limit Alarm

Field configurable analog to relay limit alarm powered by 24VAC/VDC and Input signal ranges of 0-15V, 0-30V or 0-20mA. Trip/Release Point programmed via DIP switches. LED's indicate operating status.



FC-3RLY4

Analog Input, 4-Relay, Limit Alarm

Field configurable analog to relay limit alarm powered by 24VAC/VDC and Input signal ranges of 0-15V, 0-30V or 0-20mA. Trip/Release Point programmed via DIP switches. LED's indicate operating status.



FC-ISO-D

Encoder Signal Conditioner and Optical Isolator - Differential Line Driver Output

Ideal for use with single-ended (open collector, NPN, pull-up, push-pull, totem pole) or differential line driver encoders. Three complementary inputs (A, B, Z, A-not, B-not, Z-not) are rated for 4.5-7.5 and 12-26 VDC and frequency response up to 1 MHz.

Optical isolation separates the input signals from three differential line driver outputs (A, B, Z, A-not, B-not, Z-not) rated for 5VDC.



FC-ISO-C

Encoder Signal Conditioner and Optical Isolator - Open Collector Output

Ideal for use with single-ended (open collector, NPN, pull-up, push-pull, totem pole) or differential line driver encoders. Three complementary inputs (A, B, Z, A-not, B-not, Z-not) are rated for 4.5-7.5 and 12-26 VDC and frequency response up to 1 MHz.

Optical isolation separates the input signals from three complementary open collector outputs (A, B, Z, A-not, B-not, Z-not) rated for 5-36 VDC that can be used in single-ended configurations.